

## Installation accessories for modular front design TS

### Perforated mounting strips

#### for partial doors

For retrospective external mounting. The perforated mounting strips have a 25 mm pitch pattern of holes and may be used for individual mountings on the rear side of the door, e.g. cable ducts, hose holders etc.

Hole diameter of perforated mounting strip: 4.5 mm

#### Material:

- Sheet steel, 1 mm

#### Surface finish:

- Zinc-plated

#### Supply includes:

- Assembly parts

For enclosure width mm	Length mm	For partial door height mm	Packs of	Model No.
400	298	150 – 800	10 pc(s).	<b>9671.204</b>
600	498	150 – 800	10 pc(s).	<b>9671.206</b>
800	698	150 – 800	10 pc(s).	<b>9671.208</b>



### Front trim panels, top

#### for TS

To finish off the modular front design at the top when using partial doors. The front trim panels may be removed from the outside by unscrewing. The cross member required for mounting is included with the supply of the mounted partial door.

#### Material:

- Sheet steel, 2 mm

#### Surface finish:

- Textured paint

#### Colour:

- RAL 7035

#### Protection category IP to IEC 60 529:

- IP 54

#### Supply includes:

- Assembly parts

For enclosure width mm	Height mm	Packs of	Model No.
400	100	1 pc(s).	<b>9672.314</b>
400	300	1 pc(s).	<b>9672.324</b>
600	100	1 pc(s).	<b>9672.316</b>
600	300	1 pc(s).	<b>9672.326</b>
800	100	1 pc(s).	<b>9672.318</b>
800	300	1 pc(s).	<b>9672.328</b>



### Front trim panels, bottom

#### for TS

To finish off the modular front design at the bottom when using partial doors. If version IP 2X is chosen, a roof plate with protection category IP 2X should be selected for top ventilation. The front trim panels may be removed from the outside by unscrewing.

#### Material:

- Sheet steel, 2 mm

#### Surface finish:

- Textured paint

#### Colour:

- RAL 7035

#### Supply includes:

- Front trim panel including cross member
- Assembly parts

#### Protection category IP 54

For enclosure width mm	Height mm	Packs of	Model No.
400	100	1 pc(s).	<b>9672.334</b>
400	300	1 pc(s).	<b>9672.344</b>
600	100	1 pc(s).	<b>9672.336</b>
600	300	1 pc(s).	<b>9672.346</b>
800	100	1 pc(s).	<b>9672.338</b>
800	300	1 pc(s).	<b>9672.348</b>

#### Protection category IP 2X

For enclosure width mm	Height mm	Packs of	Model No.
400	300	1 pc(s).	<b>9672.354</b>
600	300	1 pc(s).	<b>9672.356</b>
800	300	1 pc(s).	<b>9672.358</b>

#### Also required:

Roof plate IP 2X, see page 583

#### Accessories:

Upgrade kit IP 4X, see page 555

