


## Fixing disk

with stud shoulder

| Nr.   | System | A  | B      | C   | D    |    |
|-------|--------|----|--------|-----|------|----|
| 81587 | AF 16  | 7  | 12x0,5 | M4  | 8    | 5  |
| 80748 | AF 16  | 10 | 24x1   | M4  | 8    | 7  |
| 80600 | AF 25  | 15 | 24x1   | M6  | 12,5 | 10 |
| 80601 | AF 25  | 19 | 32x1   | M6  | 12,5 | 17 |
| 82822 | AF 40  | 19 | 24x1   | M10 | 20   | 28 |
| 80602 | AF 40  | 24 | 24x1   | M12 | 20   | 30 |
| 92900 | AF 40  | 24 | 32x1   | M10 | 20   | 32 |
| 80603 | AF 40  | 25 | 32x1   | M12 | 20   | 34 |
| 82827 | AF 50  | 30 | 32x1   | M12 | 25   | 45 |



## Fixing disk

for set up independant of grid

| Nr.   | System | A    | B      | C       |    |
|-------|--------|------|--------|---------|----|
| 81589 | AF 16  | 7,3  | 12x0,5 | M4      | 5  |
| 81489 | AF 16  | 10,2 | 24x1   | M4      | 10 |
| 80597 | AF 25  | 15,3 | 24x1   | M6      | 8  |
| 95905 | AF 25  | 7,7  | 24x1   | 1/4"-20 | 10 |
| 95906 | AF 25  | 15   | 24x1   | M8      | 12 |
| 95907 | AF 25  | 7,7  | 24x1   | 3/8"-16 | 11 |
| 80598 | AF 25  | 19,6 | 32x1   | M6      | 15 |
| 82770 | AF 40  | 26,2 | 24x1   | M10     | 10 |
| 82771 | AF 40  | 25,7 | 32x1   | M10     | 20 |
| 82772 | AF 50  | 30   | 24x1   | M12     | 15 |
| 82773 | AF 50  | 32   | 32x1   | M12     | 25 |

## Overview connecting disks for keyless chucks

| $\varnothing$ | A       | System | #     | B    | #     | C    | #     | D    | E   | F  | #     | G   | H    | #     | I   |
|---------------|---------|--------|-------|------|-------|------|-------|------|-----|----|-------|-----|------|-------|-----|
| 50            | M12x0,5 | AF 16  | 23646 | 8    | 23647 | 4,3  | 81587 | 8    | M4  | 7  | 81589 | M4  | 7,3  | 52111 | M4  |
| 50            | M12x0,5 | AF 25  | 29580 | 12,5 |       |      |       |      |     |    |       |     |      |       |     |
| 80            | M16x1,0 | AF 16  | 52102 | 8    | 52106 | 4,3  | 93434 | 8    | M4  | 7  | 93438 | M4  | 7    | 52112 | M4  |
| 80            | M16x1,0 | AF 25  | 52103 | 12,5 | 52107 | 6,7  | 93435 | 12,5 | M6  | 15 | 93439 | M6  | 15   | 21711 | M6  |
| 125           | M32x1,0 | AF 25  | 23238 | 12,5 | 23244 | 6,7  | 80601 | 12,5 | M6  | 19 | 80598 | M6  | 19,6 | 21711 | M6  |
| 125           | M32x1,0 | AF 40  | 23264 | 20   | 23265 | 10,7 | 92900 | 20   | M10 | 24 | 82771 | M10 | 25,7 | 52114 | M10 |
| 125           | M32x1,0 | AF 50  | 26926 | 25   | 52108 | 13,6 | 80603 | 25   | M12 | 25 | 82773 | M12 | 32   | 52115 | M12 |
| 200           | M50x1,5 | AF 40  | 52104 | 20   | 52109 | 10,7 | 93436 | 20   | M10 | 24 | 93440 | M10 | 22   | 52116 | M10 |
| 200           | M50x1,5 | AF 50  | 52105 | 25   | 52110 | 13,6 | 93437 | 25   | M12 | 25 | 93441 | M12 | 30   | 52117 | M12 |

