



... Low-Cost-Eco-

Spritzgussmuttern

Günstige schmierfreie Gewindemuttern durch Kunststoffspritzguss

Zu 100% schmierfrei und konsequent kostengünstig sind werkzeugfallend im Spritzgussverfahren hergestellte drylin® Gewindemuttern. Für die Baugröße Ø 8 und 10 können so effiziente dryspin® Steilgewinde als auch selbsthemmende Trapezgewinde in einem Guss gefertigt werden.

- Kostengünstig durch Spritzguss
- Hoher Wirkungsgrad
- Sichere Montage durch Schlüsselflächen
- dry-tech® Material iglidur® J

Typische Anwendungsbereiche:

Höhenverstellungen, Fassadenbau, Stellantriebe, Spindelmotoren, 3D-Drucker

Low-cost and lubrication-free lead screw nuts injection-moulded

drylin® lead screw nuts, which are injection-moulded off-tool, are 100% lubrication-free and therefore highly cost-effective. For sizes Ø 8 and 10, efficient dryspin® high-helix threads can also be supplied as self-locking trapezoidal threads made in one cast.

- Low-cost due to injection moulding
- High efficiency
- Secure assembly due to spanner flats
- dry-tech® material iglidur® J

Typical application areas:

Height-adjustment mechanisms, facade construction, actuators, 3D printers

Abmessungen Dimensions [mm]

Art.-Nr. Part No.	Gewinde Thread
dryspin® Steilgewinde High helix threads	
DST-JFRM-C-01-DS8X10	Ds8x10
DST-JFRM-C-01-DS8X15	Ds8x15
DST-JFRM-C-01-DS10X12	Ds10x12
DST-JFRM-C-01-DS10X25	Ds10x25
DST-JFRM-C-01-DS10X50	Ds10x50
DST-JFLM-C-01-DS8X15	Ds8x15
DST-JFLM-C-01-DS10X12	Ds10x12
DST-JFLM-C-01-DS10X25	Ds10x25
DST-JFLM-C-01-DS10X50	Ds10x50
DST-JSRM-C-01-DS8X10	Ds8x10
DST-JSRM-C-01-DS8X15	Ds8x15
DST-JSRM-C-01-DS10X12	Ds10x12
DST-JSRM-C-01-DS10X25	Ds10x25
DST-JSRM-C-01-DS10X50	Ds10x50
DST-JSLM-C-01-DS8X15	Ds8x15
DST-JSLM-C-01-DS10X12	Ds10x12
DST-JSLM-C-01-DS10X25	Ds10x25
DST-JSLM-C-01-DS10X50	Ds10x50
Trapez-/Metrische Gewinde Trapezoidal/metric threads	
JFLM-C-01-M8	M8
JFLM-C-01-TR8X1.5	Tr8x1,5

Art.-Nr. Part No.	Gewinde Thread
Trapez-/Metrische Gewinde Trapezoidal/metric threads	
JFLM-C-01-M10	M10
JFLM-C-01-TR10X2	Tr10x2
JFLM-C-01-TR10X3	Tr10x3
JFRM-C-01-M8	M8
JFRM-C-01-TR8X1.5	Tr8x1,5
JFRM-C-01-M10	M10
JFRM-C-01-TR10X2	Tr10x2
JFRM-C-01-TR10X3	Tr10x3
JFRM-C-01-TR10X4P2	Tr10x4P2
JSLM-C-01-M8	M8
JSLM-C-01-TR8X1.5	Tr8x1,5
JSLM-C-01-M10	M10
JSLM-C-01-TR10X2	Tr10x2
JSLM-C-01-TR10X3	Tr10x3
JSRM-C-01-M8	M8
JSRM-C-01-TR8X1.5	Tr8x1,5
JSRM-C-01-M10	M10
JSRM-C-01-TR10X2	Tr10x2
JSRM-C-01-TR10X3	Tr10x3
JSRM-C-01-TR10X4P2	Tr10x4P2

Lieferbar Available ab Mai from May

www.igus.de/DST-C
www.igus.eu/DST-C