

Liquid Cooling Package

Accessories for LCP CW/DX

Touchscreen display

for LCP Rack, Inline, CW

The colour display offers the opportunity of directly monitoring key LCP functions and implementing settings.

For LCP CW	Packs of	Model No.
3311.130 3311.230 3311.260 3311.530 3311.540 3311.560	1 pc(s).	3311.030



Condenser unit

The condenser unit is needed to operate the refrigerant-based LCPs, and comprises the external condenser and fan.

Refrigerant:

- R410a

For LCP DX	Packs of	Model No.
3311.410 3311.420 3311.430 3311.440	1 pc(s).	3311.360

Note:

- The pipework between the LCP DX and the condenser is not included with the supply.



Vertical shielding

for enclosure height 2000 mm

To block the airflow on the left and right of the 482.6 mm (19") level.

Length: 1900 mm

Material:

- Cellular PU foam
- Flame-inhibiting to UL 94 (HF1)
- Self-adhesive on one side

For sealing between	For enclosure width mm	Packs of	Model No.
Side panel and 482.6 mm (19") level	600	1 pc(s).	3301.380
	800	1 pc(s).	3301.390
LCP and 482.6 mm (19") level	600	1 pc(s).	3301.370
	800	1 pc(s).	3301.320



Connection hose

bottom and top

Flexible connection hose, may be cut to required length, including union nuts on both sides for connecting the LCP to existing pipework.

For LCP CW	Thread	Water connection from	Packs of	Model No.
3311.130 3311.230 3311.260 3311.530 3311.540 3311.560	1 1/2"	bottom/top	2 pc(s).	3311.040



Rear adaptor

for LCP Inline CW

May be positioned to the rear of the set forward LCP Inline to close the existing gap in the rear section.

For LCP Inline CW	Packs of	Model No.
3311.530 3311.560	1 pc(s).	3311.080



Add-on cover

for 2000 mm high LCP

For height compensation in conjunction with 2200 mm high server enclosures.

Material:

- Sheet steel

Surface finish:

- Spray-finished

Colour:

- RAL 7035

For LCP	Packs of	Model No.
3300.239, 3311.230, 3311.260, 3311.420, 3311.440, 3311.530, 3311.540, 3311.560	1 pc(s).	3301.421

