




五幅条圆轮缘手轮




按图定制

①代号	类型	安装方式	手轮主体		握柄		握柄螺纹部	
			M材质	S表面处理	M材质	S表面处理	M材质	S表面处理
HWSALD	转动	螺钉	AC4B	喷砂	A2024	喷砂	SS400	镀铬
HWSTLC	手柄型	锁紧型	FCD500	镀铬	SS400	镀铬		



HWSALD
HWSTLC



视角标准：第一视角

G1 手柄手轮拉手
合页门组件



①代号 - ②D - ③d
HWSALD - D80 - d12

型号			D ₂	L ₃	H	h	h ₁	L	L ₁	L ₂	F	F ₁	F ₂	M		M ₁	S	W	参考重量(kg/pcs)	
①代号	②D	③d												铸铁	铝合金				HWSALD	HWSTLC
HWSALD HWSTLC	80	10*	24	28	8.5	4.5	36	14	24							4	9	8	0.38	0.16
		12																		
	100	10	30	37	9.5	5.5	39	16	28	15	6	12					10	9	0.6	0.25
		12*																		
	125	12	33	55	46.5		40	17									13	8	0.9	0.35
		15*																		
	160	16	37	70.7	62.5	12.5	6.5	46	18.5	32	16						15	10.5	1.4	0.56
		20																		
	200	16	43	87.3	81			59.5	24	41	19						16.5	11	2.8	1.14
		20																		

△带*规格仅HWSTLC适用。



数量分类	小单	中大单	大单
数量	1~50	51~100	100~
交货期	通常	7工作日	现询



数量	1~9	10~
价格	100%	现询

