

磨齿直齿轮·压力角 20°

模数 3·凸缘型

大批量
订购 
bulk order


■ 模数 3·凸缘型

进口
产品



按图定制 >

① 代号	类型	材质	热处理	齿面硬度
GKEDKA	凸缘型	15CrMo	渗碳淬火	55~60HRC



订购编号示例

① 代号	-	② 模数	-	③ 齿数	-	④ 轴孔直径 dr	-
GKEDKA	-	3	-	20	-	20	-

▲ 精度等级 JIS B 1702-1 5 级。

① 代号	② 模数	③ 齿数		④ 轴孔直径 dr		G 分度圆 直径	D 齿顶圆 直径	d 齿根圆 直径	H	B	L	L ₁	H ₁	L ₂	许用扭矩 (N·m)		许用扭矩 (kgf·m)		侧隙 (mm)	质量 (kg)			
		15	18	22	25										25	30	弯曲强度	齿面强度			弯曲强度	齿面强度	
GKEDKA	3	15	18	22		45	51	37.5	36	30	45	15				247	124	25.2	12.7	0.10~0.20	0.4		
			18	20	25	54	60	46.5	45							328	187	33.4	19.1				
			20	20	25	60	66	52.5	45							384	236	39.1	24.1				
			24	20	25	72	78	64.5	45							499	353	50.9	36				
			25		25	30	75	81	67.5							55	528	386	53.9	39.3	0.12~0.22	1.03	
			30		28	35	90	96	82.5							60	677	565	69.1	57.7			
			35		30	35	105	111	97.5							60	790	745	80.6	75.9			
			36		30	35	108	114	100.5							60	820	790	83.6	80.6			
			40		30	40	120	126	112.5							70	938	988	95.6	101	0.14~0.24	2.86	
			45		30	40	135	141	127.5							70	1090	1260	111	129			
			48		35	40	144	150	136.5							70	1180	1450	120	147			
			50		32	40	150	156	142.5							70	1240	1570	126	161			
			55		35	40	165	171	157.5							70	140	20	1330	1830	135	187	4.39
			60		35	45	180	186	172.5							80	156	1470	2200	150	224		

dr		b		t	
基准尺寸	公差	基准尺寸	公差	基准尺寸	公差
18	+0.018 0	6	±0.015	2.8	+0.1 0
20	+0.021 0				
22					
25					
28		8	±0.018	3.3	+0.2 0
30					
32					
35	10				
40					
45					

