

精制联轴器·十字滑块型


定位螺丝固定型



产品特点: 主体采用 A2017 阳极氧化处理, 容许误差可调整, 轴向反作用力小, 有良好的电绝缘性, 用于阴极溅镀装置 / 零件进料器 / 缝纫机 / 娱乐器材。



①代号	轴套 [M] 材质	弹性体 [M] 材质	[S] 表面处理
CGHAJ	A2017	聚氨酯	阳极氧化处理



订购编号示例

①代号	-	② D	-	③ L	-	④ c	-	⑤ d
CGHAJ	-	6	-	8.4	-	c1	-	d2

①代号	② D	③ L	④ c ⑤ d 可选范围																	
CGHAJ	6	8.4	1	1.5	2															
	8	9.6	1	2	3															
	10	10.2		2	3	4														
	12	14.2		3	4	5														
	15	16			4	5	6	6.35	8											
	17	19.8			4	5	6	6.35	8											
	20	21.4			4	5	6	6.35	8	9.525	10	12								
	26	25.6			5	6	6.35	8	9.525	10	12	14								
	30	32.5				8	9.525	10	12	14	15	16								
	34	34					10	12	14	15	16									
	38	40						10	12	14	15	16	18	20						
	45	46							10	12	14	15	16	18	20	22				
55	57									14	15	16	18	20	22	25				
68	77												18	20	22	25	28	30	35	38

①代号	② D	F	M	紧固螺钉扭矩 (N·m)	额定扭矩 (N·m)	容许偏心 (mm)	容许偏角 (°)	容许转速 (rpm)	惯性矩 (kg·m ²)	重量 (g)
CGHAJ	6	1.3	M2	0.3	0.2	0.5	3	100000	2.2x10 ⁻⁹	0.4
	8	1.3	M2	0.3	0.5	7	3	78000	7.4x10 ⁻⁹	0.8
	10	1.4	M2	0.3	0.8	0.9	3	63000	1.9x10 ⁻⁸	1
	12	2	M3	0.7	1	1	3	52000	5.3x10 ⁻⁸	3
	15	2.2	M3	0.7	1.6	1	3	42000	1.4x10 ⁻⁷	4
	17	2.5	M3	0.7	2.2	1.2	3	37000	2.8x10 ⁻⁷	7
	20	2.9	M4	1.7	3.2	1.2	3	31000	5.7x10 ⁻⁷	9
	26	3.7	M4	1.7	6	1.5	3	24000	2.1x10 ⁻⁶	20
	30	5	M4	1.7	15	2	3	21000	5.4x10 ⁻⁶	38
	34	5.6	M5	4	16	2.5	3	18000	9.1x10 ⁻⁶	52
	38	6.1	M5	4	28	2.5	3	16000	1.6x10 ⁻⁵	69
	45	6.9	M6	7	30	3	3	14000	3.3x10 ⁻⁵	110
55	9.4	M8	15	45	4	3	11000	1.0x10 ⁻⁴	230	
68	12	M10	30	80	4.5	3	9000	3.7x10 ⁻⁴	430	

▲以上参数由最大孔径测得。