




带壳磁铁



①代号	类型	M材质	S表面处理	M材质	S表面处理	最高工作温度
MTBUK	V槽型	45#	无电解镀锌	钕磁铁	镀锌	80° C



视角标准：第一视角

▲ 吸附力、表面磁通密度为参考值。



①代号 - ②D
MTBUK - D8

①代号	②D	T	d	d1	g	h	t	吸附力 (kgf)	表面磁通密度 高斯(G)	
MTBUK	8	6	4	2	3	2	1.5	0.4	3000 ~ 3400	
	10		6					1	2600 ~ 3000	
	13		7					1.5	1900 ~ 2500	
	16	8	9.5	3	4	2	2	3	2400 ~ 2700	
	20		10					12.5	5	2200 ~ 2600
	25		13					16.5	10	2500 ~ 2900