







★ 产品特点: 可利用 b 部的槽来避让键。(该槽并非用于键的止动)。



类型	M材质	S表面处理	A附件
SCABS	一般结构用钢	四氧化三铁保护膜	2个内六角螺栓
SCAES		无电解镀锌	2个内六角螺栓(不锈钢)

▲ 如对防锈有要求, 请优先选用无电解镀锌产品。



视角标准: 第一视角

A3  
固定环



①代号 - ②D - ③B  
SCABS - D10 - B10

①代号	内径		主要尺寸								
	②D	③B	D <sub>1</sub>	M(粗牙)	d	R	a	T <sub>1</sub>	T <sub>2</sub>	T <sub>3</sub>	b
SCABS SCAES	10	10	30	M4	4.5	3.75		9	5	7	3.5
	12	10	30	M4	4.5	3.75		10	5	8.5	4.5
		10	34	M4	4.5	3.75		11.5			
	15	12	35	M5	5.5	4.5		12	6	10.5	5.5
		15		M6	6.6	6		13	8		
		10	40			4.5					
	20	12		M5	5.5	4.5		14	7	13.5	6.5
		15		M6	6.6	6	1.5	15	8		
	25	12	45	M5	5.5	4.5		17	7	16.5	
		15	50	M6	6.6	6		18	10		8.5
	30	15	55	M6	6.6	6		20		19	
	10	12	30	M5	5.5	4.5			5		3.5
	15	35	M6	6.6	6		10	6	7		
12	12	30	M5	5.5	4.5			5		8.5	
	15	35	M6	6.6	6		11	6		4.5	

▲ b部槽不是键固定槽, 而是键避空槽。



交货期 **5天发货**

数量分类	标准订单	特殊订单
	数量	1~50
交货期	5天发货	另行报价

▲ 常州东莞发货遇特殊期间交期有变更。  
▲ 部分型号为5天发货, 请以报价为准。

