


防松螺母

非金属嵌件六角锁紧螺母




■非金属嵌件六角锁紧螺母



① 代号	类型	④ 材质	⑤ 表面处理
NTWDKB	非金属嵌件六角锁紧螺母	45#	镀锌
NTWBKB		SUS304	—

▲适用标准: DIN985-1987



订购编号示例

① 代号	-	② M
NTWDKB	-	M5

型号		螺距 P	m	h	S	e (min)	
① 代号	② M						
NTWDKB NTWBKB	4	0.7	2.9	5	7	7.66	
	5	0.8	3.2		8	8.79	
	6	1	4	6	10	11.05	
	8	1.25	5.5	8	13	14.38	
	10	1.5	6.5	10	17	18.9	
	12	1.75	8	12	19	21.1	
	14	2	9.5	14	22	24.49	
	16		10.5	16	24	26.75	
	18	2.5	13	18.5	27	29.56	
	20		14	20	30	32.95	
	(14)		15		22	32	35.03
	24			24	36	39.55	
	(27)	3	17	27	41	45.2	
	(30)	3.5	19	30	46	50.85	

F6
垫
螺
片
丝
—
吊
螺
环
母