

悬臂销

法兰安装 内螺纹型




大批量
订购
bulk order

■法兰安装 内螺纹型



① 代号		④ 材质	⑤ 表面处理	⑥ 附件
圆型	对边切割型	45#	四氧化三铁保护膜	挡圈
CSFBRN	CSFBFN			弹簧钢
CSFERN	CSFECN	SUS304	-	不锈钢
CSFNRN	CSFN CN			

产品特点: 侧板螺母安装, 零件侧内螺纹紧固, 承载较高。



订购编号示例

① 代号 - ② No - ③ B - ④ L - ⑤ M - ⑥ 追加工代码
 CSFBRN - 17 - B17 - L17 - MD10 - GP

① 代号	② No	轴径		指定单位 1mm		⑤ M(粗牙)	D ₁	P	B ₁	M ₁ (粗牙)	d	h	Q	W
		D	公差 g6	③ B	④ L									
(圆型) CSFBRN CSFERN CSFN RN (对边切割型) CSFBFN CSFECN CSFN CN	6	6	-0.004	12 ~ 60	5 ~ 100	3	8	26	10	M 4	6.5	3.5	17	14
	6A		-0.012			32		23					-	
	8	-0.005	-0.014			4		28					19	15
	10					32		26					-	
	10A	10	40			23		16						
	12	12	15			36		30					-	
	13	13	16		38	26	20							
	15	15	-0.006		10 ~ 150	5 6 8	18	40	M 5	8	4.4	27	22	
	16	16	-0.017			6 8 10	19	42				31	25	
	17	17	20				44	32				28		
	18	18	21				46	34				31		
	20	20	24				48	36				32		
	22	22	26				50	39				34		
	25	25	-0.007		17 ~ 75		6 8 10 12	29	54	M 6	9.5	5.4	42	38
	30	30	-0.020			8 10 12 16	34	62	49				42	
	35	35	-0.009				39	70	55				50	
	40	40	-0.025				12 16 20	44	80				63	56
	50	50	20 ~ 75					54	90				73	70
		16 20												

△有关外螺纹的退刀槽尺寸参见外螺纹退刀槽加工尺寸表。



追加工类型	嵌入部加工	
⑥ 追加工代码	GP	
示例图		
详细说明	在底座面部分追加嵌入部加工	
	D	GP g6
	6	8
	8~30	10
35~50	12	
指定方法	GP	

C1 悬臂销 / 销轴