


平键螺纹沉孔型



①代号	类型	M材质
FKACK	A型	45#
FKBCK	B型	
FKCCK	C型	



①代号 - ②B - ③L
FKACK - B8 - L40

订购编号示例

①代号	②B	公差h9	③L								C	H公差	h	d	d ₁	b	M				
FKACK FKBCK FKCCK	8	0	35	40	45	50	55	60	65	70	80	85	90	100	0.3	7	3.3	3.3	6	8	M3
	10	-0.036	45	50	55	60	65	70	80	85	90	100	8	4.3		4.3	7.5	10	M4		
	12		50	55	60	65	70	80	85	90	100	0.5	0			12	M5				
	14		50	55	60	65	70	80	85	90	100		9	-0.090	5.3	5.3		9	14		
	15	0	50	55	60	65	70	80	85	90	100		10					15			
	16	-0.043	60	65	70	80	85	90	100						16						
	18		60	65	70	80	85	90	100	110		11	0 -0.110	6.3	6.3	11	18	M6			

L	公差
~ 50	0 -0.25
51 ~ 80	0 -0.30
81 ~ 110	0 -0.35