

# 内六角螺钉

## 平圆头型




■平圆头型



①代号	类型	[M] 材质	[H] 硬度	[S] 表面处理	强度等级
SWLAB	内六角平圆头螺钉	碳钢	37-42HRC	发黑	10.9
SWLBB		SUS304	—	—	A2-70
SWLDB		一般结构钢	—	镀锌	8.8
SWLEB		SUS316	—	—	A4-70

产品特点: 于施加较大拧紧力矩、链接强度高、头部能埋在零件内、结构要求紧凑、外形平滑的链接场合。如刨床、导轨等处。

▲适用标准: GB/T 70.2-2008  
▲相当 ISO7380



订购编号示例

①代号	-	② M	-	③ L
SWLAB	-	M5	-	L10

型号		③ L										P 螺距	D	K	S	h (min)	d	a																			
①代号	② M																																				
(碳钢) SWLAB SWLDB	2	4	5	6	8	10	12	16	20											0.4	3.5	1.3	1.35	0.6													
	2.5	4	5	6	8	10	12	16	20	25	30											0.45	4.7	1.5	1.56	0.8	2.5	0.6									
	3	4	6	8	10	12	14	16	18	20	25	30	35	45	50											0.5	5.7	1.65	2	1.04	3.6	1					
	4	6	8	10	12	16	20	25	30	35	45	50											0.7	7.6	2.2	2.5	1.3	4.7	1.4								
	5	6	8	10	12	14	16	20	25	30	35	45	50											0.8	9.5	2.75	3	1.56	5.7	1.6							
	6	8	10	12	14	16	20	25	30	35	45	50	55	60											1.0	10.5	3.3	4	2.08	6.8	2						
	8	10	12	14	16	20	25	30	35	45	50	55	60	65	70	75	80	85	90	100											1.25	14	4.4	5	2.6	9.2	2.5
	10	16	20	25	30	35	45	50	55	60	65	70	75	80	85	90	100											1.5	17.5	5.5	6	3.12	11.2	3			
	12	16	20	25	30	35	45	50	55	60	65	70	75	80	85	90	100											1.75	21	6.6	8	4.16	14.2	3.5			
16	30	35	45	50	55	60	65	70	75	80	90	100											2.0	28	8.8	10	5.2	18.2	4								

型号		③ L										P 螺距	D	K	S	h (min)	d	a																						
①代号	② M																																							
(不锈钢) SWLBB SWLEB	2.5	3	4	5	6	8	10	12	16	18	20	25											0.45	4.7	1.5	1.5	0.8	2.5	0.6 (9)											
	3	4	6	8	10	12	14	16	18	20	25	30	35	45	50											0.5	5.7	1.65	2	1.04	3.6	1								
	4	6	8	10	12	14	16	18	20	25	30	35	45	50	55	60	65	70	75											0.74	7.6	2.2	2.5	1.3	4.7	1.4				
	5	6	8	10	12	14	16	18	20	25	30	35	45	50	55	60	65	70	75	80	85	90	100											0.8	9.5	2.75	3	1.56	5.7	1.6
	6	8	10	12	14	16	18	20	25	30	35	45	50	55	60	65	70	75	80	85	90	100											1.0	10.5	3.3	4	2.08	6.8	2	
	8	12	14	16	18	20	25	30	35	45	50	55	60	65	70	75	80	85	90	100											1.25	14	4.4	5	2.6	9.2	2.5			
	10	16	18	20	22	25	30	35	45	50	55	60	65	70	75	80	85	90	100											1.5	17.5	5.5	6	3.12	11.2	3				
	12	20	25	30	35	45	50	55	60	65	70	75	80	85	90	100											1.75	21	6.6	8	4.16	14.2	3.5							

F6  
垫片/螺母  
吊环

分类目录



返回主目录

