

十字槽螺钉

十字槽沉头螺钉




■十字槽沉头螺钉



①代号	类型	[M] 材质	[S] 表面处理
SWSDC	十字槽沉头螺钉	碳钢	镀锌
SWSBC		SUS304	—

产品特点: 不锈钢材质, 坚硬不易折断, 沉头设计使紧固后的物品美观

△适用标准: GB/T 819-1985



订购编号示例

①代号	-	② M	-	③ L
SWSDC	-	M5	-	L10

型号		③ L														P 螺距	D	E		
①代号	② M																			
(碳钢) SWSDC	2.5	6	8	10	12	14	16	18	20	25						0.45	4.7	1.5		
	3	4	5	6	8	10	12	14	16	18	20	25	30	35	40	0.5	5.5	1.65		
	4	6	8	10	12	14	16	18	20	25	30	35	40	45	50	0.7	8.4	2.7		
	5	6	8	10	12	14	16	18	20	25	30	35	40	45	50	55	60	0.8	9.3	2.7
	6	8	10	12	14	16	18	20	25	30	35	40	45	50	55	60	1	11.3	3.3	
	8	10	12	14	16	18	20	25	30	35	40	45	50	55	60	1.25	15.8	4.65		
10	16	20	25	30	35	40	45	50	55	60						1.5	18.3	5		

型号		③ L														P 螺距	D	E										
①代号	② M																											
(不锈钢) SWSBC	1.6	3	4	5	6	8	10	12	14	16	18	20	25						0.35	3	1							
	2	3	4	5	6	8	10	12	14	16						0.4	3.8	1.2										
	2.5	4	5	6	8	10	12	14	16	18	20	25	30						0.45	4.7	1.5							
	3	4	5	6	8	10	12	14	16	18	20	25	30	35	40	45	50	0.5	5.5	1.65								
	4	6	8	10	12	14	16	18	20	25	30	35	40	45	50	55	60	65	70	75	80	0.7	8.4	2.7				
	5	6	8	10	12	14	16	18	20	25	30	35	40	45	50	55	60	65	70	75	80	85	90	95	100	0.8	9.3	2.7
	6	8	10	12	14	16	18	20	25	30	35	40	45	50	55	60	65	70	75	80	85	90	95	100	1	11.3	3.3	
	8	10	12	14	16	18	20	25	30	35	40	45	50	55	60	65	70	75	80	85	90	95	100	1.25	15.8	4.65		
10	16	18	20	25	30	35	40	45	50	55	60	65	70	75	80	85	90	95	100	1.5	18.3	5						

F6
垫片/吊环
螺母