



Serie 400 / 401 / 402

Gelenkköpfe Maßreihe K
Gleitpaarung: Stahl auf Stahl
Wartungspflichtig
Außengewinde
Hohe Belastungen

Innenring:

Wälzlagerstahl, gehärtet, geschliffen und poliert; Gleitoberfläche hartverchromt

Außenring:

Gelenklageraußenring aus Edelstahl, spanlos um den Ring geformt, die Schmierstoffverteilung erfolgt über die Schmiernut im Außenring

Gehäuse:

Vergütungsstahl, geschmiedet, verzinkt und chromatiert, das Gelenklager wird in das Gehäuse gepresst und beidseitig verstemmt

Schmiernippel:

DIN 3504 Form D

Lagerluft:

Reduzierte Lagerluft

Wartungs- und Bedienungsanleitung unter www.askubal.de/service/bedienungs-und-wartungsanleitungen/



Series 400 / 401 / 402

Rod ends dimension series K
Mating materials: Steel on steel
Maintenance required
Male thread
High loads

Inner ring:

Antifriction bearing steel, hardened, ground and polished, sliding face hard chromium plated

Outer ring:

Outer ring of spherical bearing made of stainless steel, swaged around the inner ring, lubricant is distributed via the lubrication groove in the outer ring

Housing:

Tempering steel, forged, galvanized and chromated, the spherical bearing is pressed into the housing and caulked at both sides

Lubricating nipple:

DIN 3504 shape D

Bearing clearance:

Reduced bearing clearance

Instruction and maintenance manual see www.askubal.de/en/service/instruction-and-maintenance-manual/