



No. 6945-11 Adaptor Plate



CAD



Order no.	Article no.	Screw (2 pieces)	F	dia. G	K	M	N	U	Weight [g]
61259	6945-11-20-08-10	M10x45	26	11	10	40	24	32,7	190
61267	6945-11-20-08-20	M10x50	26	11	20	40	24	32,7	300
61275	6945-11-32-08-10	M12x50	32	13	10	50	28	40,4	290
61283	6945-11-32-08-20	M12x60	32	13	20	50	28	40,4	485
61291	6945-11-63-08-10	M16x60	38	17	10	60	34	48,3	500
61309	6945-11-63-08-20	M16x70	38	17	20	60	34	48,3	770
63503	6945-11-94-08-20	M20x85	55	21	20	80	46	69,0	1500

Design:

Tempering steel, blued, with locating pin and two mounting bolts ISO 4762.

Application:

The adaptor plate is fitted between of the clamping head and it's base in order to obtain a different clamping height.


On request:

Special sizes available on request.

No. 6945-11 Clamping Piston, complete



CAD



Order no.	Article no.	Clamping force at 400 bar [kN]	Stroke [mm]	Vol. [cm ³]	Weight [g]
61473	6945-11-20-10	20	6	2,9	220
61481	6945-11-32-10	32	8	6,4	400
61499	6945-11-63-10	63	10	16,0	730
64089	6945-11-94-10	94	12	28,5	1200


Design:

Hardened steel, piston case hardened and ground. Cover burnished. With mounting screws.

Application:

For simple retrofitting into existing fixture body. Suitable for clamping bar No. 6945-22-20-** and clamping head No. 6945-11-**.

Installation dimensions:



Dimensions:

Order no.	Article no.	dia. A	B ±0.1	C	dia. D1	dia. D2	E	F	G	K	dia. N	P	Screw (4 pieces)	Md max. [Nm]	M x depth	V	W
61473	6945-11-20-10	25,5	13,0	40	25 +0,033	25 -0,020/-0,041	26	4	14,0	26	6,6	11,0	M6 x 12- 8.8	10	M6 x 10	40	13
61481	6945-11-32-10	32,5	16,0	50	32 +0,039	32 -0,025/-0,050	33	7	15,0	33	8,4	12,0	M8 x 20- 8.8	25	M8 x 20	50	16
61499	6945-11-63-10	45,5	21,0	60	45 +0,039	45 -0,025/-0,050	39	9	20,0	39	8,4	15,0	M8 x 20- 10.9	36	M8 x 20	60	21
64089	6945-11-94-10	55,5	28,5	70	55 +0,046	55 -0,030/-0,060	49	13	25,5	49	10,4	17,5	M10 x 25- 12.9	79	M10 x 23	80	23

Subject to technical alterations.