



Gelenklager Sonderausführung
Gleitpaarung: Stahl auf Stahl
wartungspflichtig
HO2RS

Innenring:
Wälzlagerstahl, gehärtet, geschliffen

Außenring:
Wälzlagerstahl, gehärtet, geschliffen. Zur Montage des Innenrings wird der Außenring gesprengt.

Schmierung:
Schmiernut und Schmierbohrung, die Nachschmierung kann auch über die Innenbohrung erfolgen.

Dichtung:
Mit beidseitigen Dichtringen.

Radiale Lagerluft:
Siehe technische Grundlagen Gelenklager Maßreihe E, Gleitpaarung Stahl auf Stahl.

Wartungs- und Bedienungsanleitung unter www.askubal.de/service/bedienungs-und-wartungsanleitungen/



Spherical bearing special version
Mating materials: Steel on steel
Maintenance required
HO2RS

Inner ring:
Antifriction bearing steel, hardened, ground

Outer ring:
Antifriction bearing steel, hardened, ground. Outer ring is split for assembly of inner ring.

Lubrication:
Lubrication groove and lubrication bore, relubrication is also possible through the inner bore.

Sealing:
Sealing rings at both sides.

Radial clearance:
See technical basics spherical bearings dimension series E, mating material steel on steel.

Instruction and maintenance manual see www.askubal.de/en/service/instruction-and-maintenance-manual/