



Gelenklager Sonderausführung
Gleitpaarung: Stahl auf Hochleistungsbronze
wartungspflichtig
Ausführung S

Innenring:
Wälzlagerstahl, gehärtet, geschliffen und gefinished.

Außenring:
Außendurchmesser geschliffen, Gleitfläche aus Hochleistungsbronze. Die Schmierstoffverteilung erfolgt über die Schmiernut im Außenring.

Außenteil:
Stahl, Außendurchmesser geschliffen. Gelenklager wird in das Außenteil gepresst und beidseitig gegen axiales Verschieben gesichert. Dennoch ist beim Einbau darauf zu achten, dass beide Außenringe axial abgestützt werden.

Schmierung:
Der Schmierstoff gelangt über eine Querbohrung im Außenring bzw. im Außenteil in die Schmiernut.

Wartungs- und Bedienungsanleitung unter www.askubal.de/service/bedienungs-und-wartungsanleitungen/



Spherical bearing Special version
Mating materials: Steel on high-duty bronze
Maintenance required
Version S

Inner ring:
Antifriction bearing steel, hardened, ground and polished.

Outer ring:
Outer diameter ground, sliding face made of high-duty bronze. Lubricant is distributed via the lubrication groove in the outer ring.

Outer case:
Steel, outer diameter ground. Spherical bearing is pressed into the outer case and secured at both sides against axial movement. However the two outer rings should be axial supported at mounting.

Lubrication:
The lubricant enters the lubrication groove through a cross hole in the outer ring.

Instruction and maintenance manual see www.askubal.de/en/service/instruction-and-maintenance-manual/