

# CONDUIT CONNECTORS FOR RIGID PIPING



Anaconda conduit connectors for EN-60423 norm rigid piping, nickel plated brass.



Anaconda nickel plated brass conduit connectors for metric rigid piping are meant to be used to connect the Anaconda Sealtite conduits to a rigid EN-60423 piping. By the use of a double seal ring on the pipe connection a perfect IP 67 sealing is achieved. By using a good grip mechanism on the pipe clamping ring a high pull-out strength is achieved.

### Material & Construction:

**Construction:** Nickel plated brass fitting, consisting of 9 parts (counter nut, clamping ring, ferrule, intermediate part, 2 O-rings, filler ring, pipe


clamping ring and compression nut).

**Material:** Counter nut, intermediate part, filler ring, pipe clamping ring and compression nut are made from nickel plated brass. The clamping ring is made from PA6. The ferrule is made from galvanised steel and the 2 O-rings are made from NBR rubber.

**Temperature:** -45 °C till +105 °C continuous.

**Protection class:** IP 67.

**Colour:** Metal



Anaconda straight conduit connector for EN-60423 rigid piping, nickel plated brass



Metric Pipe diam.	Sealtite Size (Inch)	Min. Internal Bore (mm)	Dimensions in mm					Standard Package	Article Number	Weight (Kg/100)
			A	C	D	E	F			
16	5/16"	8,3	43	26	16	24	26	10	705.015.0	8,7
16	3/8"	11,0	43	26	16	24	26	10	705.016.1	8,3
16	1/2"	14,0	43	29	16	27	26	10	705.018.1	8,8
20	1/2"	14,5	44	29	20	28	30	10	705.020.1	9,9
20	3/4"	18,0	46	35	20	34	30	5	705.023.1	12,5
25	1"	22,0	48	45	25	42	36	5	705.028.1	20,0
32	1.1/4"	29,0	53	53	32	50	45	2	705.035.1	29,0