

Anaconda nickel plated brass fittings for Anaconda Sealrite.

The nickel plated brass Anaconda fittings can be used with all types of Anaconda Sealrite (except CNP). This Anaconda fitting is the most used universal fitting and offers great corrosion protection in combination with a nice appearance. Because of the UL & CSA approvals the fittings are also suitable for export projects outside Europe.

Construction: Nickel plated brass fitting, consisting of 4 parts (counter nut, clamping ring, ferrule and body).

Material: Counter nut, body and ferrule are nickel plated brass with exception of size 3/8" till 1" where the ferrule is from galvanised steel. Clamping ring and inserts are made

from PA6 (red for ISO metric, blue for Pg and white for NPT).
Special approvals: UL-514B and CSA C 22.2 (combined UL/CSA file # E 234207).

Suitable for use in hazardous environments according NEC 501-4B Class I, Division 2; Class II, Division 1 and 2; Class III, Division 1 and 2.


Temperature: -45 °C till +105 °C continuous (cable-hose-fittings are -40 °C till +100 °C).

Protection class: IP 67 (dust-proof, water-tight), with cable-hose fittings an IP 68 rate on the switchbox can be obtained. Swivel fittings are limited to IP 65.

Colour: Metal.



ISO straight fitting, male, nickel plated brass.




Thread ISO	Sealtite Size (inch)	Min. Internal Bore (mm)	Dimensions in mm					Standard Package	Article Number	Weight (Kg/100)
			A	B	C	D	E			
M12 x 1,5	1/4"	5,2	33	10	22	-	20	50	812.012.1*	4,8
M16 x 1,5	5/16"	8,3	35	12	26	-	24	50	812.015.1*	4,8
M20 x 1,5	5/16"	8,3	36	13	26	-	24	50	812.014.1*	5,1
M16 x 1,5	3/8"	10,2	35	12	26	-	24	50	812.016.1	4,8
M20 x 1,5	3/8"	10,2	36	13	26	-	24	50	812.017.1	5,1
M20 x 1,5	1/2"	13,9	37	13	29	-	27	50	812.020.1	5,9
M25 x 1,5	3/4"	18,5	40	15	35	-	33	25	812.025.1	7,9
M32 x 1,5	1"	23,8	46	15	45	-	43	10	812.032.1	17,5
M40 x 1,5	1.1/4"	31,8	52	16	54	-	52	5	812.040.1	27,9
M50 x 1,5	1.1/2"	36,8	56	18	63	-	60	5	812.050.1	42,3
M63 x 1,5	2"	47,8	66	20	77	-	74	4	812.063.1	73,5
M75 x 1,5	2.1/2"	59,0	72	24	95	-	90	4	812.075.1*	134,4
M90 x 1,5	3"	73,5	80	28	110	-	105	2	812.090.1*	172,8
M105 x 2	4"	94,0	92	32	145	-	135	2	812.105.1*	300,0

* Fittings for 1/4", 5/16", 2.1/2", 3" and 4" conduit without UL/CSA approval.



ISO straight fitting, small design, male, nickel plated brass.



Thread ISO	Sealtite Size (inch)	Min. Internal Bore (mm)	Dimensions in mm					Standard Package	Article Number	Weight (Kg/100)
			A	B	C	D	E			
M12 x 1,5	1/4"	5,2	33	10	19	-	17	50	812.012.2	2,8
M16 x 1,5	1/4"	5,2	35	12	19	-	19	50	812.013.2	3,4
M12 x 1,5	5/16"	8,3	33	10	22	-	20	50	812.011.2	3,6
M16 x 1,5	5/16"	8,3	35	12	22	-	20	50	812.015.2	3,8
M20 x 1,5	5/16"	8,3	36	13	22	-	24	25	812.014.2	4,2