



Anaconda IP 40 nickel plated brass fittings for Multiflex FCEN

These nickel plated brass Anamet fittings are similar to the standard fittings for Multitite type FCE, but the caps are adjusted to be used with Multiflex type FCEN. The 2-piece fittings are universal, offer excellent corrosion protection in combination with a good appearance. In addition to the mentioned straight fittings, other types or custom made solutions are also possible.



Material & Construction:

Construction: Nickel plated brass fitting, consisting of 2 parts (cap and body).

Material: Cap and body are nickel plated brass.


Temperature: -55 °C till +260 °C continuous.

Protection class: IP 40.

Colour: Metal.

ANACONDA
MULTIFLEX


FITTINGS FOR
TYPE FCEN
IP 40



ISO straight fitting, fixed, male, nickel plated brass.



Thread ISO	FCEN Size (DN)	Min. Internal Bore (mm)	Dimensions in mm					Standard Package	Article Number	Weight (Kg/100)
			A	B	C	D	E			
M12 x 1,5	12	8,5	26	10	18	-	-	10	256.012.0	1,8
M16 x 1,5	12	8,5	26	10	18	-	-	10	256.015.0	2,0
M16 x 1,5	16	11,2	27	10	20	-	-	10	256.016.0	2,3
M20 x 1,5	16	11,2	27	10	22	-	-	10	256.017.0	2,6
M20 x 1,5	20	15,2	27	10	24	-	-	10	256.020.0	3,0
M25 x 1,5	25	19,2	32	12	30	-	-	5	256.025.0	5,4
M32 x 1,5	32	25,9	35	13	38	-	-	5	256.032.0	8,1
M40 x 1,5	40	34,8	41	14	48	-	-	2	256.040.0	15,0
M50 x 1,5	50	44,8	45	15	60	-	-	2	256.050.0	22,4
M63 x 1,5	50	44,8	46	16	70	-	-	2	256.060.0	28,6



ISO straight fitting, swivel, male, nickel plated brass.



Thread ISO	FCEN Size (DN)	Min. Internal Bore (mm)	Dimensions in mm					Standard Package	Article Number	Weight (Kg/100)
			A	B	C	D	E			
M12 x 1,5	12	8,5	34	10	18	-	18	10	256.112.0	2,4
M16 x 1,5	12	8,5	34	10	18	-	18	10	256.115.0	3,1
M16 x 1,5	16	11,2	36	10	20	-	20	10	256.116.0	3,9
M20 x 1,5	16	11,2	36	10	20	-	22	10	256.117.0	4,2
M20 x 1,5	20	15,2	37	10	24	-	24	10	256.120.0	4,9
M25 x 1,5	25	19,2	43	12	30	-	30	5	256.125.0	8,8
M32 x 1,5	32	25,9	47	13	38	-	38	5	256.132.0	13,3
M40 x 1,5	40	34,8	56	14	48	-	48	2	256.140.0	25,1
M50 x 1,5	50	44,8	60	15	60	-	60	2	256.150.0	36,7
M63 x 1,5	50	44,8	61	16	60	-	70	2	256.160.0	47,1