



Description: Energy saving and cost-effective lightning system to be fixed with the screws or adhesive tape provided. The power output allows lights to be connected to each other by using the serial cable included. Up to a maximum power of 100 W can be serial connected.

Lamp type: LED.

Light colour: 4000 K (neutral white).

Operating voltage: 220 V - 240 V ~, 50/60 Hz.

Operating temperature: -5 °C ... +45 °C.

Connections: Infeed, 2-pole. Through wiring, 2-pole.

Material: Body polycarbonate, end caps ABS, Protection cap PMMA.

Approvals: CE, EAC.

Delivery: 1 light with power cable 1.75 m long, one connection cable 140 mm long to connect lights to each other, plus mounting materials.

Operating voltage	Luminosity	Power consumption	Dimensions	CatalogNumber
220V-240V~, 50/60 Hz	330 Lm	4W	277 x 43 x 28 mm	TL4001-4W
220V-240V~, 50/60 Hz	750 Lm	9W	538 x 43 x 28 mm	TL4001-9W