


Safety Luminaire

FlexiTech SE CGLine+




FlexiTech SE CGLine+

- LED self-contained luminaire with Automatic Test and individual monitoring (CGLine+) for reduced inspection effort
- Safety luminaire, light distribution optimized for escape route application
- Non obtrusive design and slim housing (31.2 mm)
- Good lighting performance and spacing in a compact housing
- Possibility to modify the light distribution by changing the optical lens (option)
- Same aesthetic in IP43 and IP65 versions
- Light output selectable in two steps in mains operation (eg. theater: 10 lm, supermarket: 100 lm) and additional setting (30%, 70%, 100%)
- Selectable operating time (1/1,5/2/3h operation)
- Selectable operation mode (M or NM) via external switch
- Large working space, cable entries in flexible material and spirit level for easy and fast installation
- Transparent base plate with honeycomb footprint for easy replacement of existing products (IP4x use only)
- Low eco footprint thanks to eco designed luminaire, low consumption and Lithium battery
- Life span: 10 years, proved with 1 year aging test @ 70°C ambient temperature
- No component replacement during 10 years
- Simple fault analysis and status display via bicolor LED, testing button (magnet) and supervision solutions
- Complete range of accessories (Recess Kit for Ceiling, Recessed Box for plaster and brick wall, Wire Guard, Plexi Plate)
- Other colours available on demand

FlexiTech SE



Dimensions in mm



Luminous flux Φ_e/Φ_N at end of rated operating time	150-300 lm versions: 100% @ 1h, 68% @ 1.5h, 50% @ 2h, 42% @ 3h 600 lm versions: 100% @ 1h, 68% @ 1.5h, 50% @ 2h, 33% @ 3h
Illumination in mains mode	10 or 100lm setting via switch, and possible additional setting via magnet (30%, 70%, 100%)
Operation	Maintained / Non-Maintained (via external switch)
Testing system	Automatic Test in compliance with EN 62034 Connection possible to the CGLine+ monitoring system
Housing	
Type of mounting	Surface-mounting
Material	Polycarbonate
Colour	White RAL9003
Degree of protection	IP43 & IP65 / IK07
Terminals	Screwless terminals for flexible and rigid wires From 0,5 to 2,5 mm ²
Connection voltage	220 - 240 V AC, 50/60 Hz
Permissible ambient temperature	5°C to 35°C for 10 years lifetime
Battery	LifePo
Light source	LED
Dimensions	120 × 228 × 31.2 mm
Insulation Class	II

Ordering details


Order code	IP	IK	Duration (h)	lm in emergency				lm in mains	Operation	Consumption		Battery	Weight (kg)
				1h	1.5h	2h	3h			NM WVA	M 100 lm WVA		
FT2SE150CGL13	43	7	1/1,5/2/3	150	100	75	60	10 or 100	MNM	0,4W / 1VA	2W / 5 VA	FT-BATLL2	0.4
FT2SE150CGL13IP	65	7	1/1,5/2/3	150	100	75	60	10 or 100	MNM	0,4W / 1VA	2W / 5 VA	FT-BATLL2	0.4
FT2SE300CGL13	43	7	1/1,5/2/3	300	200	150	125	10 or 100	MNM	0,4W / 1VA	2W / 5 VA	FT-BATLL3	0.4
FT2SE300CGL13IP	65	7	1/1,5/2/3	300	200	150	125	10 or 100	MNM	0,4W / 1VA	2W / 5 VA	FT-BATLL3	0.4
FT2SE600CGL13	43	7	1/1,5/2/3	600	400	300	200	10 or 100	MNM	0,4W / 1VA	2W / 5 VA	FT-BATLL3	0.4
FT2SE600CGL13IP	65	7	1/1,5/2/3	600	400	300	200	10 or 100	MNM	0,4W / 1VA	2W / 5 VA	FT-BATLL3	0.4

Accessories

	FT2-RKC	Recess Kit for Ceiling, compatible with FlexiTech SE and FlexiTech ED (ceiling position)
	FT2-WG	Wire Guard, compatible with FlexiTech SE and FlexiTech ED
	FT2SE-RB	Recessed Box for plaster and brick compatible with FlexiTech SE
	FT2SE-PP2	Plexi Plate, legend height 10cm, 4 Non adhesive pictos (D,L,R,U), ISO format, compatible with FlexiTech SE
	FT2SE-LO	Lens with light distribution optimized for Open area, compatible with FlexiTech SE
	40071352379	Eaton Magnet for lighting configuration and manual tests
	FT-BATLL2	Battery Pack, LifePo long life 3,2V / 1,5Ah
	FT-BATLL3	Battery Pack, LifePo long life 3,2V / 3Ah

FlexiTech SE - Spacing data for flux value: 75 lm

150 lumens variants configured @2 hours



Light distribution curve

FlexiTech SE, asymmetric distribution : 1 lux (0.5 lux)


Ceiling mounting, measurement at floor level, battery operation ,distances in m

Escape route illumination

Mounting height [m]	Lux level directly under				
2,5		1,2 (2,2)	4,4 (6,1)	0,8 (4,7)	7,6 (11,7)
3,0		0,6 (2,0)	4,0 (6,2)	0,3 (5,0)	6,7 (12,6)

Open area illumination

Mounting height [m]	Lux level directly under				
2,5		0,5 (0,7)	4,4 (6,1)	1,1 (5,1)	10,3 (12,2)
3,0		0,5 (0,5)	4,7 (6,3)	0,7 (1,4)	7,8 (13,4)
3,5		0,7 (0,5)	4,9 (6,2)	0,5 (1,5)	7,3 (14,5)
4,0		0,5 (0,6)	5,1 (6,6)	0,5 (0,8)	6,7 (11,3)



Light distribution curve

FlexiTech SE, with optional lens for open area, symmetric distribution : 1 lux (0.5 lux)

Ceiling mounting, measurement at floor level, battery operation ,distances in m

Escape route illumination


Mounting height [m]	Lux level directly under				
2,5	4	2,4 (3,2)	6,4 (8,1)	2,4 (3,2)	6,5 (8,2)
3,0	2,8	2,4 (3,3)	6,7 (8,6)	2,4 (3,3)	6,7 (8,7)
3,5	2	2,3 (3,4)	6,8 (9,0)	2,2 (3,4)	6,8 (9,1)
4,0	1,5	2,1 (3,5)	6,9 (9,4)	1,9 (3,4)	6,9 (9,4)

Open area illumination

Mounting height [m]	Lux level directly under				
2,5		2,1 (2,6)	5,7 (7,1)	2,1 (2,5)	5,6 (7,0)
3,0		2,1 (2,6)	6,2 (7,6)	1,9 (2,6)	5,9 (7,5)
3,5		1,9 (2,6)	6,3 (8,0)	2,0 (2,7)	6,3 (8,0)
4,0		1,8 (2,7)	6,6 (8,4)	1,8 (2,7)	6,5 (8,3)
4,5		1,5 (2,6)	6,7 (8,7)	1,6 (2,7)	6,7 (8,7)
5,0		1,2 (2,5)	6,9 (9,0)	1,3 (2,6)	6,7 (8,9)
5,5		0,8 (2,4)	7,1 (9,2)	0,7 (2,5)	6,5 (9,1)
6,0		0,5 (2,2)	6,9 (9,4)	0,7 (2,3)	6,3 (9,3)
6,5		0,8 (1,8)	7,1 (9,5)	0,5 (2,0)	5,4 (9,5)

FlexiTech SE - Spacing data for flux value: 100 lm

150 lumens variants configured @1,5 hours



Light distribution curve

FlexiTech SE, asymmetric distribution : 1 lux (0.5 lux)


Ceiling mounting, measurement at floor level, battery operation ,distances in m

Escape route illumination

Mounting height [m]	Lux level directly under				
2,5		1,6 (2,6)	5,1 (6,8)	4,1 (5,2)	10,4 (12,6)
3,0		1,3 (2,5)	5,0 (7,1)	0,8 (5,5)	8,4 (13,7)

Open area illumination

Mounting height [m]	Lux level directly under				
2,5		0,6 (0,5)	5,2 (6,8)	0,8 (5,5)	11,0 (13,2)
3,0		0,5 (0,6)	5,3 (7,1)	0,6 (6,0)	10,3 (14,4)
3,5		0,6 (0,7)	5,5 (7,3)	0,5 (1,4)	8,9 (15,5)
4,0		1,2 (1,0)	5,9 (7,3)	0,5 (1,1)	8,1 (16,4)
4,5		0,6 (0,5)	5,8 (7,6)	0,5 (0,8)	8,0 (13,3)



Light distribution curve

FlexiTech SE, with optional lens for open area, symmetric distribution : 1 lux (0.5 lux)

Ceiling mounting, measurement at floor level, battery operation ,distances in m

Escape route illumination


Mounting height [m]	Lux level directly under				
2,5	5	2,7 (3,5)	7,1 (8,8)	2,7 (3,6)	7,2 (9,0)
3,0	3,5	2,8 (3,7)	7,5 (9,4)	2,8 (3,8)	7,5 (9,6)
3,5	2,5	2,8 (3,9)	7,7 (9,9)	2,8 (3,9)	7,7 (10,1)
4,0	2	2,7 (3,9)	7,9 (10,4)	2,6 (3,9)	7,9 (10,5)
4,5	1,6	2,5 (4,0)	8,0 (10,8)	2,3 (4,0)	7,9 (10,8)

Open area illumination

Mounting height [m]	Lux level directly under				
2,5		2,2 (2,8)	6,2 (7,7)	2,3 (2,7)	6,2 (7,6)
3,0		2,3 (2,9)	6,7 (8,3)	2,3 (2,9)	6,6 (8,2)
3,5		2,2 (3,0)	7,0 (8,8)	2,3 (3,0)	7,0 (8,7)
4,0		2,4 (3,0)	7,6 (9,2)	1,9 (3,1)	7,0 (9,2)
4,5		2,0 (3,0)	7,5 (9,6)	2,1 (3,1)	7,5 (9,6)
5,0		1,9 (3,0)	7,9 (9,9)	1,7 (3,1)	7,5 (9,9)
5,5		1,4 (2,9)	7,8 (10,2)	1,7 (3,0)	7,8 (10,2)
6,0		1,0 (2,8)	7,9 (10,5)	1,4 (2,9)	7,8 (10,4)
6,5		0,5 (2,6)	8,0 (10,7)	0,9 (2,7)	7,6 (10,6)
7,0		0,5 (2,4)	8,0 (10,8)	0,6 (2,6)	7,2 (10,8)

FlexiTech SE - Spacing data for flux value: 125 lm

300 lumens variants configured @3 hours



Light distribution curve

FlexiTech SE, asymmetric distribution : 1 lux (0.5 lux)


Ceiling mounting, measurement at floor level, battery operation ,distances in m

Escape route illumination

Mounting height [m]	Lux level directly under				
2,5		1,9 (2,8)	5,6 (7,3)	4,5 (5,5)	11,1 (13,4)
3,0		1,7 (2,9)	5,7 (7,7)	1,3 (6,0)	11,9 (14,6)
3,5		1,3 (2,7)	5,5 (8,0)	0,8 (6,3)	9,0 (15,6)

Open area illumination

Mounting height [m]	Lux level directly under				
2,5		0,5 (0,8)	5,7 (7,4)	4,9 (5,8)	11,7 (13,9)
3		0,5 (0,8)	5,8 (7,8)	1,1 (6,3)	12,8 (15,2)
3,5		0,7 (0,7)	6,0 (8,1)	0,7 (1,0)	10,7 (16,4)
4		0,7 (0,8)	6,2 (8,2)	0,5 (1,1)	9,8 (17,5)
4,5		1,0 (0,6)	6,4 (8,1)	0,5 (1,4)	9,3 (18,6)



Light distribution curve

FlexiTech SE, with optional lens for open area, symmetric distribution : 1 lux (0.5 lux)

Ceiling mounting, measurement at floor level, battery operation ,distances in m

Escape route illumination

Mounting height [m]	Lux level directly under				
2,5	6	3,0 (3,8)	7,6 (9,4)	3,0 (3,9)	7,7 (9,6)
3	4,2	3,1 (4,0)	8,1 (10,1)	3,1 (4,1)	8,2 (10,3)
3,5	3,4	3,1 (4,2)	8,5 (10,7)	3,1 (4,2)	8,5 (10,9)
4	2,6	3,1 (4,3)	8,7 (11,2)	3,1 (4,3)	8,7 (11,4)
4,5	2	3,0 (4,4)	8,8 (11,6)	2,9 (4,4)	8,8 (11,8)
5	1,7	2,8 (4,5)	8,9 (12,0)	2,6 (4,4)	8,9 (12,0)
5,5	1,4	2,6 (4,4)	8,9 (12,2)	2,3 (4,4)	8,8 (12,2)


Open area illumination

Mounting height [m]	Lux level directly under				
2,5		2,4 (3,0)	6,7 (8,2)	2,4 (2,9)	6,6 (8,1)
3,0		2,5 (3,1)	7,2 (8,8)	2,5 (3,1)	7,1 (8,8)
3,5		2,5 (3,2)	7,6 (9,4)	2,5 (3,2)	7,5 (9,4)
4,0		2,7 (3,2)	8,2 (9,9)	2,2 (3,3)	7,6 (9,9)
4,5		2,4 (3,3)	8,2 (10,3)	2,4 (3,4)	8,1 (10,3)
5,0		2,2 (3,3)	8,4 (10,7)	2,3 (3,4)	8,3 (10,7)
5,5		2,0 (3,4)	8,6 (11,2)	2,1 (3,2)	8,5 (10,9)
6,0		1,6 (3,3)	8,7 (11,5)	1,9 (3,2)	8,7 (11,2)
6,5		1,3 (3,0)	8,8 (11,6)	1,6 (3,2)	8,7 (11,6)
7,0		0,6 (2,9)	8,8 (11,8)	1,3 (3,1)	8,7 (11,8)
7,5		0,5 (2,7)	9,0 (12,0)	0,7 (2,9)	8,3 (12,0)

FlexiTech SE - Spacing data for flux value: 150 lm

150 lumens variants configured @1 hour

300 lumens variants configured @2 hours



Light distribution curve

FlexiTech SE, asymmetric distribution : 1 lux (0.5 lux)


Ceiling mounting, measurement at floor level, battery operation ,distances in m

Escape route illumination

Mounting height [m]	Lux level directly under				
2,5		2,2 (3,0)	6,1 (7,8)	4,7 (5,8)	11,7 (14,1)
3,0		2,0 (3,1)	6,2 (8,3)	5,0 (6,3)	12,6 (15,3)
3,5		1,7 (3,1)	6,2 (8,6)	1,2 (6,7)	11,0 (16,4)
4,0		1,2 (2,9)	5,9 (8,8)	0,7 (7,0)	9,7 (17,4)

Open area illumination

Mounting height [m]	Lux level directly under				
2,5		0,8 (0,7)	6,1 (7,9)	5,2 (6,1)	12,2 (14,6)
3,0		0,6 (0,6)	6,3 (8,3)	1,5 (6,6)	13,4 (16,0)
3,5		0,7 (0,7)	6,3 (8,7)	1,2 (1,1)	14,4 (17,2)
4,0		0,5 (0,6)	6,6 (8,9)	0,8 (1,2)	11,4 (18,4)
4,5		0,6 (0,6)	6,8 (9,0)	0,5 (1,1)	10,7 (19,5)
5,0		0,9 (0,6)	7,0 (8,8)	0,5 (1,8)	10,2 (20,2)
5,5		0,6 (0,7)	7,1 (9,3)	0,5 (0,9)	9,8 (16,3)
6,0		0,5 (0,7)	5,9 (9,5)	0,8 (0,6)	10,1 (15,4)
6,5		0,5 (0,7)	4,3 (9,6)	0,9 (0,5)	10,8 (15,0)



Light distribution curve

FlexiTech SE, with optional lens for open area, symmetric distribution : 1 lux (0.5 lux)

Ceiling mounting, measurement at floor level, battery operation ,distances in m

Escape route illumination

Mounting height [m]	Lux level directly under				
2,5	8	3,2 (4,0)	8,1 (9,9)	3,2 (4,1)	8,2 (10,2)
3,0	5,5	3,3 (4,3)	8,6 (10,7)	3,3 (4,4)	8,7 (10,9)
3,5	4	3,4 (4,5)	9,0 (11,4)	3,4 (4,6)	9,1 (11,6)
4,0	3	3,5 (4,7)	9,4 (11,9)	3,4 (4,7)	9,4 (12,1)
4,5	2,5	3,4 (4,8)	9,5 (12,4)	3,3 (4,8)	9,5 (12,6)
5,0	2	3,3 (4,8)	9,7 (12,8)	3,1 (4,8)	9,6 (12,9)
5,5	1,6	3,1 (4,9)	9,8 (13,2)	2,8 (4,9)	9,7 (13,2)
6,0		2,8 (4,9)	9,7 (13,4)	2,5 (4,8)	9,6 (13,4)


Open area illumination

Mounting height [m]	Lux level directly under				
2,5		2,6 (3,1)	7,1 (8,6)	2,5 (3,1)	7,0 (8,6)
3,0		2,6 (3,3)	7,6 (9,3)	2,7 (3,3)	7,5 (9,3)
3,5		2,7 (3,4)	8,0 (9,9)	2,7 (3,4)	8,0 (9,9)
4,0		2,6 (3,5)	8,4 (10,5)	2,7 (3,5)	8,4 (10,4)
4,5		2,6 (3,5)	8,7 (11,0)	2,7 (3,6)	8,7 (10,9)
5,0		2,6 (3,6)	9,0 (11,4)	2,6 (3,6)	8,9 (11,3)
5,5		2,3 (3,6)	9,2 (11,8)	2,5 (3,6)	9,2 (11,7)
6,0		2,2 (3,8)	9,4 (12,5)	2,3 (3,3)	9,3 (11,7)
6,5		1,8 (3,7)	9,5 (12,7)	2,1 (3,3)	9,5 (12,1)
7,0		1,4 (3,4)	9,6 (12,7)	1,8 (3,5)	9,6 (12,6)
7,5		0,8 (3,2)	9,6 (12,9)	1,5 (3,4)	9,6 (12,8)
8,0		0,5 (3,1)	10,0 (13,1)	0,6 (3,2)	9,2 (13,0)

FlexiTech SE - Spacing data for flux value: 200 lm

300 lumens variants configured @1,5 hours

600 lumens variants configured @3 hours



Light distribution curve

FlexiTech SE, asymmetric distribution : 1 lux (0.5 lux)

Ceiling mounting, measurement at floor level, battery operation ,distances in m

Escape route illumination

Mounting height [m]	Lux level directly under				
2,5	4	2,6 (3,4)	6,8 (8,6)	5,2 (6,3)	12,6 (15,2)
3,0	2,5	2,5 (3,5)	7,1 (9,1)	5,5 (6,9)	13,7 (16,6)
3,5	1	2,3 (3,6)	7,2 (9,6)	5,8 (7,3)	14,6 (17,8)
4,0		2,0 (3,6)	7,2 (9,9)	1,4 (7,7)	12,9 (18,9)


Open area illumination

Mounting height [m]	Lux level directly under				
2,5		0,6 (0,8)	6,8 (8,6)	5,5 (6,5)	13,2 (15,7)
3,0		0,6 (0,7)	7,2 (9,2)	0,9 (7,1)	14,4 (17,2)
3,5		0,8 (0,8)	7,3 (9,7)	1,6 (1,2)	15,5 (18,5)
4,0		0,6 (0,7)	7,3 (10,0)	1,2 (8,0)	16,6 (19,8)
4,5		1,1 (0,6)	7,7 (10,2)	0,5 (2,2)	13,2 (21,0)
5,0		0,6 (0,6)	7,8 (10,4)	0,6 (1,1)	12,5 (22,1)
5,5		1,0 (0,5)	8,0 (10,3)	0,5 (1,8)	12,0 (23,2)
6,0		0,5 (0,5)	8,0 (10,5)	0,5 (1,2)	11,8 (20,4)
6,5		0,5 (0,5)	8,4 (10,9)	0,5 (0,5)	10,9 (18,4)
7,0		0,5 (0,7)	6,6 (11,0)	0,9 (0,6)	11,8 (17,7)
7,5		0,5 (0,7)	4,9 (11,1)	0,9 (0,5)	12,5 (17,3)

FlexiTech SE - Spacing data for flux value: 200 lm

300 lumens variants configured @1,5 hours

600 lumens variants configured @3 hours



Light distribution curve

FlexiTech SE, with optional lens for open area, symmetric distribution : 1 lux (0.5 lux)

Ceiling mounting, measurement at floor level, battery operation ,distances in m

Escape route illumination

Mounting height [m]	Lux level directly under				
2,5	10	3,5 (4,4)	8,8 (10,8)	3,6 (4,5)	9,0 (11,1)
3,0	7	3,7 (4,7)	9,4 (11,7)	3,8 (4,8)	9,6 (11,9)
3,5	5	3,9 (5,0)	9,9 (12,4)	3,9 (5,1)	10,1 (12,6)
4,0	4	3,9 (5,2)	10,4 (13,1)	3,9 (5,3)	10,5 (13,3)
4,5	3	4,0 (5,4)	10,8 (13,6)	4,0 (5,4)	10,8 (13,9)
5,0	2,5	4,0 (5,5)	11,0 (14,1)	3,9 (5,5)	11,0 (14,4)
5,5	2	3,9 (5,5)	11,1 (14,6)	3,7 (5,5)	11,1 (14,8)
6,0		3,7 (5,6)	11,2 (15,0)	3,4 (5,6)	11,2 (15,1)
6,5		3,5 (5,6)	11,3 (15,3)	3,2 (5,6)	11,2 (15,3)
7,0		3,2 (5,6)	11,2 (15,5)	2,8 (5,5)	11,1 (15,5)


Open area illumination

Mounting height [m]	Lux level directly under				
2,5		2,8 (3,4)	7,7 (9,3)	2,8 (3,4)	7,6 (9,3)
3,0		2,9 (3,6)	8,3 (10,1)	2,9 (3,6)	8,2 (10,1)
3,5		2,9 (3,7)	8,8 (10,8)	3,0 (3,7)	8,8 (10,8)
4,0		3,0 (3,9)	9,2 (11,4)	3,1 (3,9)	9,2 (11,4)
4,5		3,0 (4,0)	9,6 (12,0)	3,1 (4,0)	9,6 (11,9)
5,0		3,1 (4,0)	10,1 (12,5)	2,9 (4,1)	9,8 (12,4)
5,5		2,9 (4,0)	10,2 (12,9)	3,1 (4,2)	10,2 (12,9)
6,0		2,8 (4,0)	10,5 (13,3)	2,9 (4,2)	10,4 (13,3)
6,5		2,6 (4,1)	10,7 (13,7)	2,7 (4,1)	10,6 (13,6)
7,0		2,4 (4,0)	10,9 (14,0)	2,5 (4,1)	10,8 (14,0)
7,5		2,0 (3,9)	11,0 (14,3)	2,3 (4,1)	11,0 (14,3)
8,0		1,7 (3,9)	11,1 (14,6)	2,0 (4,0)	11,0 (14,5)
8,5		1,0 (3,6)	11,1 (14,8)	1,8 (3,9)	11,1 (14,8)
9,0		0,7 (3,5)	11,4 (15,0)	1,1 (3,8)	10,8 (15,0)

FlexiTech SE - Spacing data for flux value: 300 lm

300 lumens variants configured @1 hour

600 lumens variants configured @2 hours



Light distribution curve

FlexiTech SE, asymmetric distribution : 1 lux (0.5 lux)

Ceiling mounting, measurement at floor level, battery operation, distances in m

Escape route illumination

Mounting height [m]	Lux level directly under				
2,5	5,5	3,0 (3,9)	7,8 (9,6)	5,8 (7,0)	14,1 (16,8)
3,0	4	3,1 (4,1)	8,3 (10,4)	6,3 (7,7)	15,3 (18,4)
3,5	3	3,1 (4,3)	8,6 (11,0)	6,7 (8,2)	16,4 (19,8)
4,0	2	2,9 (4,4)	8,8 (11,5)	7,0 (8,7)	17,4 (21,1)
4,5		2,7 (4,4)	8,9 (11,9)	7,1 (9,1)	18,2 (22,3)


Open area illumination

Mounting height [m]	Lux level directly under				
2,5		0,7 (1,2)	7,9 (9,7)	6,1 (7,1)	14,6 (17,3)
3,0		0,9 (1,0)	8,4 (10,5)	1,0 (7,7)	15,9 (19,0)
3,5		0,8 (0,7)	8,7 (11,1)	7,0 (8,4)	17,2 (20,6)
4,0		0,7 (0,6)	8,9 (11,6)	1,8 (8,9)	18,4 (22,0)
4,5		0,7 (0,6)	9,0 (12,0)	1,2 (9,3)	19,5 (23,3)
5,0		0,6 (0,7)	8,8 (12,3)	1,8 (9,8)	20,5 (24,5)
5,5		0,8 (0,6)	9,4 (12,5)	0,5 (2,6)	16,3 (25,7)
6,0		0,6 (0,6)	9,5 (12,7)	0,6 (1,3)	15,5 (26,8)
6,5		0,5 (0,6)	9,6 (12,7)	0,5 (1,5)	15,1 (27,9)
7,0		1,4 (0,5)	10,1 (12,5)	0,5 (2,1)	14,2 (29,0)
7,5		0,7 (0,9)	9,9 (13,1)	0,5 (0,8)	14,2 (23,9)

FlexiTech SE - Spacing data for flux value: 300 lm

300 lumens variants configured @1 hour

600 lumens variants configured @2 hours



Light distribution curve

FlexiTech SE, with optional lens for open area, symmetric distribution : 1 lux (0.5 lux)

Ceiling mounting, measurement at floor level, battery operation ,distances in m

Escape route illumination


Mounting height [m]	Lux level directly under				
2,5	16	4,0 (5,0)	9,9 (12,0)	4,1 (5,1)	10,2 (12,4)
3,0	11	4,3 (5,4)	10,7 (13,1)	4,4 (5,5)	10,9 (13,5)
3,5	7,5	4,5 (5,7)	11,4 (14,0)	4,6 (5,8)	11,6 (14,3)
4,0	6	4,7 (6,0)	11,9 (14,8)	4,7 (6,1)	12,1 (15,1)
4,5	5	4,8 (6,2)	12,4 (15,5)	4,8 (6,3)	12,6 (15,8)
5,0	4	4,8 (6,4)	12,8 (16,1)	4,8 (6,5)	12,9 (16,4)
5,5	3	4,9 (6,6)	13,2 (16,7)	4,9 (6,6)	13,2 (17,0)
6,0		4,9 (6,7)	13,4 (17,2)	4,8 (6,7)	13,4 (17,5)
6,5		4,8 (6,8)	13,5 (17,6)	4,6 (6,8)	13,5 (17,9)
7,0		4,7 (6,8)	13,6 (18,1)	4,4 (6,8)	13,6 (18,2)
7,5		4,5 (6,9)	13,8 (18,4)	4,2 (6,9)	13,7 (18,5)
8,0		4,3 (6,9)	13,8 (18,7)	3,9 (6,9)	13,7 (18,7)

Open area illumination

Mounting height [m]	Lux level directly under				
2,5		3,1 (3,8)	8,6 (10,4)	3,1 (3,7)	8,6 (10,4)
3,0		3,3 (4,0)	9,3 (11,3)	3,3 (4,0)	9,3 (11,3)
3,5		3,4 (4,2)	10,0 (12,1)	3,4 (4,2)	9,9 (12,1)
4,0		3,4 (4,4)	10,5 (12,9)	3,5 (4,3)	10,5 (12,8)
4,5		3,5 (4,5)	11,0 (13,5)	3,6 (4,5)	10,9 (13,5)
5,0		3,5 (4,6)	11,4 (14,1)	3,7 (4,7)	11,4 (14,1)
5,5		3,6 (4,7)	11,8 (14,7)	3,6 (4,8)	11,7 (14,6)
6,0		3,5 (4,7)	12,1 (15,2)	3,7 (4,9)	12,1 (15,1)
6,5		3,5 (4,8)	12,4 (15,6)	3,6 (5,0)	12,4 (15,6)
7,0		3,4 (4,8)	12,7 (16,1)	3,5 (4,9)	12,6 (16,0)
7,5		3,2 (4,9)	12,9 (16,4)	3,4 (5,0)	12,9 (16,4)
8,0		3,0 (5,1)	13,1 (17,2)	3,3 (4,6)	13,1 (16,4)
8,5		2,9 (4,8)	13,3 (17,1)	3,0 (5,0)	13,2 (17,1)
9,0		2,5 (4,7)	13,4 (17,4)	2,8 (5,0)	13,4 (17,4)
9,5		2,4 (4,8)	13,9 (17,9)	2,2 (4,7)	13,2 (17,5)

FlexiTech SE - Spacing data for flux value: 400 lm

600 lumens variants configured @1,5 hours



Light distribution curve

FlexiTech SE, asymmetric distribution : 1 lux (0.5 lux)

Ceiling mounting, measurement at floor level, battery operation, distances in m

Escape route illumination


Mounting height [m]	Lux level directly under				
2,5	8	3,4 (4,3)	8,6 (10,4)	6,3 (7,6)	15,2 (18,1)
3	5,8	3,5 (4,6)	9,1 (11,3)	6,9 (8,3)	16,6 (19,8)
3,5	4	3,6 (4,8)	9,6 (12,1)	7,3 (8,9)	17,8 (21,4)
4		3,6 (4,9)	9,9 (12,7)	7,7 (9,5)	18,9 (22,8)
4,5		3,4 (5,1)	10,1 (13,2)	8,0 (10,0)	19,9 (24,1)
5		3,2 (5,1)	10,2 (13,6)	8,1 (10,4)	20,8 (25,3)
5,5		2,9 (5,1)	10,2 (13,9)	2,1 (10,7)	19,7 (26,4)

Open area illumination

Mounting height [m]	Lux level directly under				
2,5		0,9 (0,9)	8,6 (10,5)	6,5 (7,6)	15,7 (18,7)
3,0		0,8 (1,2)	9,2 (11,4)	7,1 (8,3)	17,2 (20,4)
3,5		0,6 (0,9)	9,7 (12,2)	7,5 (8,9)	18,6 (22,1)
4,0		0,8 (0,6)	10,0 (12,8)	8,0 (9,5)	19,8 (23,7)
4,5		0,9 (0,6)	10,3 (13,3)	1,0 (10,1)	20,9 (25,1)
5,0		0,7 (0,7)	10,4 (13,7)	1,2 (10,5)	22,1 (26,4)
5,5		0,5 (0,5)	10,4 (14,1)	1,2 (1,4)	23,2 (27,7)
6,0		1,0 (0,5)	10,6 (14,3)	0,9 (11,5)	20,4 (28,9)
6,5		0,5 (0,7)	10,9 (14,5)	0,6 (2,6)	18,5 (30,0)
7,0		0,6 (0,7)	11,0 (14,7)	0,6 (1,3)	17,8 (31,1)
7,5		0,6 (0,6)	11,1 (14,7)	0,5 (1,6)	17,4 (32,2)
8,0		1,8 (0,5)	11,8 (14,5)	0,5 (2,2)	16,2 (33,3)
8,5		0,5 (0,6)	11,3 (15,0)	0,5 (0,9)	16,7 (28,6)

FlexiTech SE - Spacing data for flux value: 600 lm

600 lumens variants configured @1 hour



Light distribution curve

FlexiTech SE, asymmetric distribution : 1 lux (0.5 lux)

Ceiling mounting, measurement at floor level, battery operation, distances in m

Escape route illumination


Mounting height [m]	Lux level directly under				
2,5	11	3,9 (4,8)	9,6 (11,8)	7,0 (8,4)	16,8 (20,0)
3,0	8	4,1 (5,2)	10,4 (12,7)	7,7 (9,2)	18,4 (22,0)
3,5	6	4,3 (5,5)	11,0 (13,6)	8,2 (9,9)	19,8 (23,7)
4,0	4,5	4,4 (5,8)	11,5 (14,4)	8,7 (10,6)	21,1 (25,3)
4,5	3,5	4,4 (5,9)	11,9 (15,1)	9,1 (11,1)	22,3 (26,8)
5,0		4,4 (6,1)	12,2 (15,6)	9,5 (11,7)	23,4 (28,2)
5,5		4,2 (6,2)	12,4 (16,1)	9,8 (12,2)	24,4 (29,5)
6,0		4,0 (6,3)	12,5 (16,5)	10,0 (12,6)	25,2 (30,7)
6,5		3,7 (6,3)	12,5 (16,9)	2,9 (13,0)	26,0 (31,8)

Open area illumination

Mounting height [m]	Lux level directly under				
2,5		0,9 (1,3)	9,7 (11,9)	7,1 (8,3)	17,4 (20,6)
3,0		1,1 (1,3)	10,5 (12,8)	7,7 (9,1)	19,0 (22,6)
3,5		0,8 (1,3)	11,1 (13,7)	8,4 (9,8)	20,6 (24,4)
4,0		0,8 (1,3)	11,6 (14,5)	8,9 (10,4)	22,0 (26,1)
4,5		0,7 (0,8)	12,0 (15,2)	9,4 (11,1)	23,3 (27,8)
5,0		0,5 (0,8)	12,3 (15,8)	9,8 (11,7)	24,6 (29,3)
5,5		0,7 (0,7)	12,6 (16,3)	1,2 (12,2)	25,7 (30,7)
6,0		0,8 (0,5)	12,7 (16,7)	1,5 (12,7)	26,8 (32,1)
6,5		1,2 (0,7)	12,8 (17,1)	1,3 (1,8)	27,7 (33,3)
7,0		1,0 (0,8)	12,6 (17,4)	1,9 (1,8)	28,8 (34,5)

FlexiTech SE - Spacing data for flux value: 600 lm

600 lumens variants configured @1 hour



Light distribution curve

FlexiTech SE, with optional lens for open area, symmetric distribution : 1 lux (0.5 lux)

Ceiling mounting, measurement at floor level, battery operation ,distances in m

Escape route illumination

Mounting height [m]	Lux level directly under				
2,5	30	5,0 (6,0)	12,0 (14,5)	5,1 (6,2)	12,4 (15,1)
3,0	20	5,4 (6,5)	13,1 (15,8)	5,5 (6,7)	13,5 (16,4)
3,5	16	5,7 (7,0)	14,0 (17,0)	5,8 (7,2)	14,3 (17,5)
4,0	12,5	6,0 (7,4)	14,8 (18,0)	6,1 (7,6)	15,1 (18,6)
4,5	10	6,2 (7,8)	15,5 (19,0)	6,3 (7,9)	15,8 (19,5)
5,0	8	6,4 (8,1)	16,1 (19,9)	6,5 (8,2)	16,4 (20,4)
5,5	7	6,6 (8,3)	16,7 (20,7)	6,6 (8,5)	17,0 (21,1)
6,0	5,5	6,7 (8,6)	17,2 (21,4)	6,7 (8,8)	17,5 (21,8)
6,5	5	6,8 (8,8)	17,6 (22,1)	6,8 (9,0)	17,9 (22,5)
7,0	4	6,8 (9,0)	18,1 (22,7)	6,8 (9,1)	18,2 (23,1)
7,5	3,5	6,9 (9,2)	18,4 (23,3)	6,9 (9,3)	18,5 (23,7)
8,0	3,2	6,9 (9,4)	18,7 (23,8)	6,9 (9,4)	18,7 (24,3)
8,5	2,8	6,9 (9,5)	18,9 (24,3)	6,8 (9,5)	18,9 (24,8)
9,0	2,5	6,8 (9,5)	19,1 (24,8)	6,6 (9,5)	19,1 (25,2)
9,5		6,7 (9,6)	19,2 (25,2)	6,4 (9,6)	19,2 (25,5)
10,0		6,6 (9,7)	19,3 (25,6)	6,2 (9,6)	19,3 (25,9)

Open area illumination

Mounting height [m]	Lux level directly under				
2,5		3,8 (4,6)	10,4 (12,6)	3,7 (4,3)	10,4 (12,5)
3,0		4,0 (4,7)	11,3 (13,5)	4,0 (4,8)	11,3 (13,9)
3,5		4,2 (5,0)	12,1 (14,5)	4,2 (5,1)	12,1 (14,9)
4,0		4,4 (5,4)	12,9 (15,6)	4,3 (5,3)	12,8 (15,6)
4,5		4,6 (5,6)	13,5 (16,5)	4,5 (5,5)	13,5 (16,4)
5,0		4,7 (5,8)	14,1 (17,2)	4,7 (5,8)	14,1 (17,2)
5,5		4,7 (6,0)	14,7 (18,0)	4,8 (5,9)	14,6 (17,9)
6,0		4,7 (6,2)	15,2 (18,7)	4,9 (6,1)	15,2 (18,6)
6,5		4,8 (6,3)	15,7 (19,3)	4,9 (6,2)	15,6 (19,2)
7,0		4,9 (6,3)	16,1 (19,9)	5,0 (6,4)	16,0 (19,9)
7,5		4,9 (6,3)	16,5 (20,4)	5,0 (6,5)	16,4 (20,5)
8,0		4,8 (6,5)	16,8 (21,0)	5,0 (6,6)	16,8 (20,9)
8,5		5,1 (6,5)	17,5 (21,5)	4,7 (6,7)	16,8 (21,4)
9,0		4,9 (6,5)	17,7 (22,0)	4,7 (6,8)	17,2 (21,9)
9,5		4,7 (6,6)	17,7 (22,4)	4,9 (6,8)	17,7 (22,3)
10,0		4,6 (6,7)	18,0 (23,0)	4,8 (6,7)	17,9 (22,6)