

Fan Heater, EGL

- Description:** Heater with fan to be fixed as desired, but preferably in vertical position to prevent condensation. The fan assists the natural convection for fast distribution of the heat in large enclosures. Mounting clip for 35 mm DIN rail (EN60715).
- Heating element:** PTC resistor, self regulating and temperature limiting.
- Fan life:** 40.000 h at 25°C.
- Material:** Plastic, and anodised aluminium profile.
- Operating temperature:** -40°C to +70°C. The heating capacity is for ambient temperature 20°C.
- Connection:** Plug terminal connection (2 x 0.5-2.5 mm²).
- Protection:** IP 20, Class I (earthed).
- Approvals:** CE, EAC, cULus_UL Listed.
- Pack quantity:** 1 piece.



Capacity (W)	Starting current (A)	L (mm)	Voltage (V)	Item no.
250	2.2	187	104-126 V AC	EGL250UL115
250	1.1	187	207-258 V AC	EGL250UL230
400	3.6	227	104-126 V AC	EGL400UL115
400	1.8	227	207-258 V AC	EGL400UL230

