

General Accessories

Enclosure light, LTS

- Description:** Energy saving lighting system suitable for all types of panels and enclosures, especially where space is at a premium. It is made of light grey plastic (ABS-PC) according to UL94 V-0. The lamp can be mounted on its narrow or broad surface using screws, or magnetically in any position in a mild steel enclosure. It has electronic ballast, and its life service is of 10,000 h. An integrated electrical socket enables the use of additional appliances and it is provided with a protection cap.
- Lamp type:** Compact fluorescent lamp, 2G7 socket.
- Luminosity:** 900 Lm.
- Power consumption:** 11 W.
- Operating temperature:** -20°C to +50°C.
- Dimensions:** 345 x 91 x 40 mm.
- Connections:** Terminal 2.5 mm² with cable clamp, torque 0.8Nm max.

Operating voltage	Socket type	Approvals	Item no.
230 V, 50/60 Hz	Schuko	CE, EAC	LTS11
230 V, 50/60 Hz	France/Belgium	CE, EAC	LTS11FR
230 V, 50/60 Hz	Switzerland	CE, EAC	LTS11CH
230 V, 50/60 Hz	UK/Ireland	CE, EAC	LTS11UK
120 V, 50/60 Hz	USA/Canada	CE, EAC, cULus	LTS11USAUL

