


[1.4301]

Stainless Steel A2 / Stainless Steel C1



Dome Head <
closed <

DIN EN ISO 16585

d	l +1		No.		
3,2	6,0	0,5 - 1,5	10.908.032.060	500	
	8,0	1,0 - 3,5	10.908.032.080	500	
	9,5	2,5 - 5,0	10.908.032.095	500	
	12,0	4,5 - 7,0	10.908.032.120	500	
d_k 6,0 ±0,3	d_m 1,9	k 1,0 ±0,3	3,3 mm	2000 N	2400 N
4,0	6,0	0,5 - 1,5	10.908.040.060	500	
	8,0	1,0 - 3,0	10.908.040.080	500	
	9,5	2,5 - 4,5	10.908.040.095	500	
	12,0	4,5 - 7,0	10.908.040.120	500	
	16,0	8,0 - 11,0	10.908.040.160	500	
d_k 8,0 ±0,3	d_m 2,3	k 1,4 ±0,3	4,1 mm	3000 N	4000 N

d	l +1		No.		
4,8	8,0	0,5 - 4,0	10.908.048.080	500	
	9,5	2,5 - 5,0	10.908.048.095	500	
	12,0	4,5 - 7,5	10.908.048.120	500	
	16,0	6,0 - 11,0	10.908.048.160	500	
	20,0	9,0 - 14,5	10.908.048.200	500	
d_k 9,5 ±0,3	d_m 2,9	k 1,7 ±0,3	4,9 mm	4500 N	5500 N
6,4	10,0	2,5 - 5,0	10.908.064.100	250	
	12,0	4,5 - 6,5	10.908.064.120	250	
	16,0	6,0 - 10,5	10.908.064.160	250	
	18,0	7,5 - 11,5	10.908.064.180	250	
d_k 12,5 ±0,3	d_m 3,8 ±0,05	k 2,7	6,5 mm	6500 N	8000 N