




# Standard Blindniet ALFO® Serie 10.708



[1.4301]



## Edelstahl A2 / Edelstahl A2/A3



Senkkopf <  
offen <

DIN EN ISO 15984

d	l +1		Nr.	
<b>3,2</b>	6,0	1,5 - 3,0	10.708.320.060	500
	8,0	3,0 - 5,0	10.708.320.080	500
	10,0	5,0 - 7,0	10.708.320.100	500
	12,0	6,5 - 8,5	10.708.320.120	500

<b>dk</b> 6,0 -0,4	<b>dm</b> 1,9	3,3 mm	1800 N	2500 N
--------------------	---------------	--------	--------	--------

<b>4,0</b>	6,0	1,0 - 2,5	10.708.400.060	500
	8,0	2,5 - 4,5	10.708.400.080	500
	10,0	4,5 - 6,5	10.708.400.100	500
	12,0	6,5 - 8,5	10.708.400.120	500
	14,0	8,5 - 10,5	10.708.400.140	500
	16,0	10,0 - 12,0	10.708.400.160	500
	18,0	11,5 - 14,0	10.708.400.180	500
20,0	13,5 - 16,0	10.708.400.200	500	

NEU

NEU

<b>dk</b> 7,5 -0,5	<b>dm</b> 2,5	4,1 mm	2750 N	3550 N
--------------------	---------------	--------	--------	--------

d	l +1		Nr.	
<b>4,8</b>	8,0	2,0 - 4,0	10.708.480.080	500
	10,0	4,0 - 6,0	10.708.480.100	500
	12,0	6,0 - 8,5	10.708.480.120	500
	16,0	8,0 - 11,0	10.708.480.160	500

<b>dk</b> 9,0 -0,5	<b>dm</b> 2,9	4,9 mm	4250 N	5400 N
--------------------	---------------	--------	--------	--------

<b>5,0</b>	8,0	2,0 - 4,0	10.708.500.080	500
	10,0	4,0 - 6,0	10.708.500.100	500
	12,0	6,0 - 8,5	10.708.500.120	500
	16,0	8,0 - 11,0	10.708.500.160	500

<b>dk</b> 9,3 -0,5	<b>dm</b> 2,9	5,1 mm	4700 N	5800 N
--------------------	---------------	--------	--------	--------