





SÄULENGESTELL




201.26.



Führungsart



Bestell-Nr. Teil 2
Wahlweise ohne bzw.
mit Zapfengewinde
im Oberteil



201.26. Säulengestell

Bestell-Nummer Teil 1*	Arbeitsfläche													
	$a_1 \times b_1$	a_2	b_2	c_1	c_2	c_3	d_2	d_3	e	e_1	f	l	r	M
201.26.125.100.□□□.□□	125 x 100	165	140	50	40	90	25	24	125	206	110	160 - 500	30	24x1.5
201.26.160.100.□□□.□□	160 x 100	200	140	50	40	90	25	24	160	229	110	160 - 500	30	24x1.5
201.26.160.125.□□□.□□	160 x 125	200	165	56	40	90	32	30	160	259	139	180 - 500	37	24x1.5
201.26.200.125.□□□.□□	200 x 125	240	165	56	40	90	32	30	200	286	139	180 - 500	37	24x1.5
201.26.200.160.□□□.□□	200 x 160	240	200	56	50	100	32	30	200	312	174	200 - 500	37	30x2

*Bestell-Nummer Teil 2 = Führungsart und Führungssäulen-Typ/-Länge ergänzen
 Bestell-Beispiel siehe Anfang des Kapitels A Guss-Säulengestelle