






Blind Rivet Nut SSM-R-KLSK

Series 10.843



Steel

Small Countersunk Head <
 Round Shank <
 Open <
 knurled <



C4C [1.0303]

M		l	No.	
M3	0,3 - 1,5	8,5	10.843.030.150	500
	1,0 - 3,5	10,5	10.843.030.350	500
D 5,0	k 0,4	dk 6,0	l1 max. 5,5	↑ 4000 N
M4	1,0 - 2,0	10,0	10.843.040.200	500
	2,0 - 4,0	12,0	10.843.040.400	500
D 6,0	k 0,4	dk 7,0	l1 max. 8,0	↑ 4800 N
M5	0,5 - 3,0	12,0	10.843.050.300	500
	2,5 - 4,5	13,0	10.843.050.450	500
D 7,0	k 0,5	dk 8,0	l1 max. 9,0	↑ 8000 N

NEW

NEW

M		l	No.	
M6	0,5 - 3,0	13,5	10.843.060.300	500
	3,5 - 6,0	17,5	10.843.060.600	500
D 9,0	k 0,5	dk 10,0	l1 max. 14,5	↑ 12000 N
M8	0,7 - 4,0	16,0	10.843.080.400	500
	3,5 - 6,0	18,0	10.843.080.600	500
D 11,0	k 0,5	dk 12,0	l1 max. 16,0	↑ 18000 N
M10	1,5 - 4,5	21,5	10.843.100.450	250
	3,0 - 6,0	23,0	10.843.100.600	250
D 13,0	k 0,5	dk 14,0	l1 max. 18,5	↑ 25000 N
M12	1,0 - 4,0	24,0	10.843.120.400	100
D 16,0	k 0,6	dk 17,0	l1 max. 20,0	↑ 40000 N