


VITE DI APPOGGIO DADO ESAGONALE DIN 6330 B

2140.02.




2140.02. Vite di appoggio

N. d'ordine	M	d ₂	d ₃	k	l
2140.02.10	10	16	30	8	39
2140.02.12	12	20	36	10	48
2140.02.16	16	25	42	13	55
2140.02.20	20	25	50	16	69
2140.02.24	24	34	60	20	87

Materiale:

bonificato, classe di resistenza 8.8

2140.32.



2140.32. Dado esagonale DIN 6330 B

N. d'ordine	M	e	m	s
2140.32.08	M8	15	12	13
2140.32.10	M10	18,4	15	16
2140.32.12	M12	20,7	18	18
2140.32.14	M14	24,2	21	21
2140.32.16	M16	27,7	24	24
2140.32.18	M18	31,2	27	27
2140.32.20	M20	34,6	30	30
2140.32.22	M22	39,2	33	34
2140.32.24	M24	41,5	36	36
2140.32.30	M30	53,1	45	46

Materiale:

bonificato, classe di resistenza 10.9

Nota:

Utilizzare le rondelle del tipo DIN 6340.