




Blind Rivet Nut ESM

Series 10.859

Stainless Steel A2

- > Countersunk Head
- > Round Shank
- > Open



[1.4567]

M		l	No.	
M4	1,5 - 4,0	12,0	10.859.040.400	500
D 6,0	k 1,5	dk 9,0	l₁ max. 8,0	4 Nm 7000 N
M5	1,5 - 4,5	13,5	10.859.050.450	500
	4,5 - 6,0	15,0	10.859.050.600	500
D 7,0	k 1,5	dk 10,0	l₁ max. 8,5	6 Nm 11000 N
M6	1,5 - 4,5	16,0	10.859.060.450	500
	4,5 - 6,5	18,0	10.859.060.650	500
D 9,0	k 1,5	dk 12,0	l₁ max. 10,0	11 Nm 16000 N

NEW

NEW

M		l	No.	
M8	1,5 - 4,5	18,0	10.859.080.450	500
	4,5 - 6,5	20,0	10.859.080.650	250
D 11,0	k 1,5	dk 14,0	l₁ max. 11,5	24 Nm 27000 N
M10	1,5 - 4,0	22,0	10.859.100.400	250
	D 13,0	k 1,6	dk 16,0	l₁ max. 14,5
M12	1,7 - 4,5	26,0	10.859.120.400	250
	D 16,0	k 2,0	dk 19,0	l₁ max. 18,0

NEW