




# Écrous à sertir en aveugle ESM-KLSK

Série 10.802



**inox A2**

tête affleurante <  
cylindrique lisse <  
ouvert <

[1.4567]

M		I	N°		
<b>M4</b>	0,5 - 2,5	11,0	10.802.040.250	500	
<b>D</b> 6,0	<b>k</b> 0,5	<b>dk</b> 7,0	<b>l<sub>1</sub> max.</b> 8,0	4 Nm	6500 N
<b>M5</b>	0,5 - 3,0	12,0	10.802.050.300	500	
<b>D</b> 7,0	<b>k</b> 0,5	<b>dk</b> 8,0	<b>l<sub>1</sub> max.</b> 8,5	6 Nm	10000 N
<b>M6</b>	0,5 - 3,0	14,0	10.802.060.300	500	
<b>D</b> 9,0	<b>k</b> 0,5	<b>dk</b> 10,0	<b>l<sub>1</sub> max.</b> 10,0	11 Nm	15000 N

M		I	N°		
<b>M8</b>	0,5 - 3,0	16,0	10.802.080.300	500	
<b>D</b> 11,0	<b>k</b> 0,5	<b>dk</b> 12,0	<b>l<sub>1</sub> max.</b> 11,5	24 Nm	25000 N
<b>M10</b>	1,0 - 3,5	19,2	10.802.100.350	250	
<b>D</b> 13,0	<b>k</b> 0,7	<b>dk</b> 14,0	<b>l<sub>1</sub> max.</b> 14,0	50 Nm	38000 N