


电动输送带

2195.402.



2195.402. 电动输送带

b	500	750	1,000	1,250	1,500	1,750	2,000	2,250	2,500	2,750	3,000	3,250	3,500	3,750	4,000
a															
30										●	●	●	●	●	●
50										●	●	●	●	●	●
75								●	●	●	●	●	●	●	●
100								●	●	●	●	●	●	●	●
125							●	●	●	●	●	●	●	●	●
150							●	●	●	●	●	●	●	●	●
175						●	●	●	●	●	●	●	●	●	●
200						●	●	●	●	●	●	●	●	●	●
225						●	●	●	●	●	●	●	●	●	●
250					●	●	●	●	●	●	●	●	●	●	●
275				●	●	●	●	●	●	●	●	●	●	●	●
300				●	●	●	●	●	●	●	●	●	●	●	●
350	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●
400	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●
450	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●
500	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●

带负载:

带宽 a	千克每延米
30- 50- 75	5
100-125-150	10
175-200-225	14
250-275-300	17
350-400-450	20
500	24

更多信息, 请参见说明书和订购指南。

订购示例:

电动输送带	= 2195.
型号 402	= 402.
带宽	a = 100 mm = 100.
额定带长	b = 2500 mm = 2500.
输送带速度	= 1
电机 400 v	= 3
电机位置	= 1
电机控制装置	= 1
订购号	= 2195.402. 100. 2500. 1 3 1 1