






Blind Rivet Nut HEXATOP®-E-FK

Series 10.877



Stainless Steel A2

- > Flat Head
- > Partial Hexagonal Shank
- > Open



[1.4567]

M		I	No.		
M3	0,5 - 2,0	9,0	10.877.030.200	500	
SW 5,0	k 0,8	d _k 8,0	l ₁ max. 6,5	⌀ 2 Nm	↑ 4000 N
M4	0,5 - 2,5	11,0	10.877.040.250	500	
SW 6,0	k 1,0	d _k 9,0	l ₁ max. 8,5	⌀ 5 Nm	↑ 6500 N
M5	0,5 - 3,0	12,0	10.877.050.300	500	
SW 7,0	k 1,0	d _k 10,0	l ₁ max. 9,0	⌀ 7 Nm	↑ 10000 N

NEW

M		I	No.		
M6	0,5 - 3,0	14,0	10.877.060.300	500	
SW 9,0	k 1,5	d _k 12,0	l ₁ max. 10,0	⌀ 13 Nm	↑ 17000 N
M8	0,5 - 3,0	16,0	10.877.080.300	250	
SW 11,0	k 1,5	d _k 14,5	l ₁ max. 11,5	⌀ 25 Nm	↑ 27000 N
M10	1,0 - 3,5	19,0	10.877.100.350	250	
SW 13,0	k 2,0	d _k 16,5	l ₁ max. 13,5	⌀ 55 Nm	↑ 39000 N