





# Standard Blindniet ALFO® Serie 10.700



**Aluminium / Stahl**



- > Senkkopf
- > offen



3,0 - 3,2 mm EN AW - 5719 [AlMg5]  
4,0 mm EN AW - 5754 [AlMg3]

**DIN EN ISO 15978**

d	l +1		Nr.	
<b>3,0</b>	5,0	1,5 - 3,0	10.700.300.050	500
	6,0	2,0 - 4,0	10.700.300.060	500
	8,0	3,5 - 6,0	10.700.300.080	500
	10,0	5,0 - 7,5	10.700.300.100	500
	12,0	7,0 - 9,0	10.700.300.120	500
<b>d<sub>k</sub> 6,0 -0,4</b>	<b>d<sub>m</sub> 1,7</b>	3,1 mm	660 N	900 N
<b>3,2</b>	6,0	1,5 - 3,5	10.700.320.060	500
	8,0	3,0 - 5,5	10.700.320.080	500
	10,0	5,0 - 7,5	10.700.320.100	500
	12,0	7,0 - 9,0	10.700.320.120	500
	16,0	9,0 - 13,0	10.700.320.160	500
<b>d<sub>k</sub> 6,2 -0,4</b>	<b>d<sub>m</sub> 1,9</b>	3,3 mm	660 N	1100 N
<b>4,0</b>	6,0	1,5 - 3,5	10.700.400.060	500
	8,0	2,0 - 5,5	10.700.400.080	500
	10,0	5,0 - 7,0	10.700.400.100	500
	12,0	6,5 - 9,0	10.700.400.120	500
	16,0	8,5 - 12,5	10.700.400.160	500
	18,0	12,0 - 14,5	10.700.400.180	500
<b>d<sub>k</sub> 7,5 -0,5</b>	<b>d<sub>m</sub> 2,0</b>	4,1 mm	1120 N	1420 N

d	l +1		Nr.	
<b>4,8</b>	10,0	4,0 - 6,5	10.700.480.100	500
	12,0	6,0 - 8,0	10.700.480.120	500
	16,0	8,0 - 12,0	10.700.480.160	500
	20,0	12,0 - 15,5	10.700.480.200	500
<b>d<sub>k</sub> 9,0 -0,5</b>	<b>d<sub>m</sub> 2,7</b>	4,9 mm	1480 N	1950 N
<b>5,0</b>	8,0	2,0 - 5,0	10.700.500.080	500
	10,0	4,0 - 6,5	10.700.500.100	500
	12,0	6,0 - 8,0	10.700.500.120	500
	14,0	7,5 - 10,0	10.700.500.140	500
	16,0	8,0 - 12,0	10.700.500.160	500
	18,0	11,5 - 13,5	10.700.500.180	500
	20,0	12,0 - 15,5	10.700.500.200	500
	25,0	15,0 - 20,5	10.700.500.250	500
	30,0	20,0 - 25,5	10.700.500.300	500
35,0	25,0 - 30,0	10.700.500.350	250	
<b>d<sub>k</sub> 9,3 -0,5</b>	<b>d<sub>m</sub> 2,7</b>	5,1 mm	1650 N	2000 N

NEU

NEU