



Blind Rivet Bolt RIFBOLT®



Series 10.883 **NEW**

From winter 2014/15



Steel

- > Small Countersunk Head
- > Round Shank
- > knurled



M	$\frac{+}{-}$	l	l ₂	N°		
M4	0,5 - 2,0	10,5	10,0	10.883.043.010	500 NEW	
l ₁ max. 5,0		D 6,0	d _k 6,8	k 0,5	8000 N	↓ 7000 N
M5	0,5 - 2,0	12,5	15,0	10.883.053.015	500 NEW	
l ₁ max. 6,0		D 7,0	d _k 8,0	k 0,6	10000 N	↓ 9500 N

M	$\frac{+}{-}$	l	l ₂	N°		
M6	0,5 - 3,0	14,5	20,0	10.883.063.020	500 NEW	
l ₁ max. 7,0		D 9,0	d _k 10,0	k 0,6	14000 N	↓ 12000 N
M8	1,0 - 3,0	17,5	20,0	10.883.083.020	250 NEW	
l ₁ max. 9,0		D 11,0	d _k 12,0	k 0,6	24000 N	↓ 15000 N

l₂ = length of the screw after setting; it depends on grip range and tool adjustment