




Blind Rivet Bolt RIFBOLT®


Series 10.884 **NEW**

Steel

- > Flat Head
- > Round Shank



From winter 2014/15



| M | $\frac{+}{-}$ | l | l ₂ | N° | |
|---|---------------|------|----------------|----------------|-----|
| M5 | 0,5 - 2,0 | 13,0 | 15,0 | 10.884.053.015 | 500 |
| l_1 max. 6,0 D 7,0 d _k 10,0 k 1,0 10000 N 8,5 Nm 9500 N | | | | | |
| M6 | 0,5 - 2,5 | 15,0 | 20,0 | 10.884.063.020 | 500 |
| l_1 max. 7,0 D 9,0 d _k 12,0 k 1,2 14000 N 15 Nm 12000 N | | | | | |

NEW

NEW

| M | $\frac{+}{-}$ | l | l ₂ | N° | |
|--|---------------|------|----------------|----------------|-----|
| M8 | 0,5 - 3,0 | 18,0 | 20,0 | 10.884.083.020 | 250 |
| l_1 max. 9,0 D 11,0 d _k 15,0 k 1,5 24000 N 26 Nm 15000 N | | | | | |

NEW

l₂ = length of the screw after setting; it depends on grip range and tool adjustment