




Blind Rivet Nut EFM-R

Series 10.848



Stainless Steel A2

Flat Head <
 Round Shank <
 Open <
 Knurled <

[1.4567]

M		l	No.	
M3	0,5 - 2,0	9,0	10.848.030.200	500
	2,0 - 3,5	9,0	10.848.030.350	500
D 5,0	k 0,8	dk 8,0	l₁ max. 7,0	↓ 4000 N
M4	0,5 - 2,5	11,0	10.848.040.250	500
	2,5 - 4,0	12,5	10.848.040.400	500
D 6,0	k 0,8	dk 9,0	l₁ max. 8,0	↓ 6500 N
M5	0,5 - 3,0	12,0	10.848.050.300	500
	3,0 - 4,5	13,5	10.848.050.450	500
D 7,0	k 1,0	dk 10,0	l₁ max. 8,5	↓ 10000 N

NEW

NEW

NEW

M		l	No.	
M6	0,5 - 3,0	14,0	10.848.060.300	500
	3,0 - 5,0	16,0	10.848.060.500	500
D 9,0	k 1,5	dk 12,0	l₁ max. 10,0	↓ 17000 N
M8	0,5 - 3,0	16,0	10.848.080.300	500
	3,0 - 5,5	18,5	10.848.080.550	250
D 11,0	k 1,5	dk 15,0	l₁ max. 12,0	↓ 25000 N
M10	1,0 - 3,5	19,0	10.848.100.350	250
	3,5 - 6,0	21,5	10.848.100.600	250
D 13,0	k 2,0	dk 17,0	l₁ max. 14,0	↓ 38000 N

NEW