

d1	d2	b1	d3	b2	d1 <sup>3)</sup>		Einpressbohrung		Wellenmaße		Art.-Nr.
					max.	min.	max.	min.	max.	min.	
7/8	1	3/4	1.2500	.0620	.8791	.8757	1.0005	.9997	.8741	.8729	<b>QFI-1416-12</b>
7/8	1	1	1.2500	.0620	.8791	.8757	1.0005	.9997	.8741	.8729	<b>QFI-1416-16</b>
1	1 1/8	1/2	1.3750	.0620	1.0041	1.0007	1.1255	1.1247	.9991	.9979	<b>QFI-1618-08</b>
1	1 1/8	1	1.3750	.0620	1.0041	1.0007	1.1255	1.1247	.9991	.9979	<b>QFI-1618-16</b>
1	1 1/8	1 1/2	1.3750	.0620	1.0041	1.0007	1.1255	1.1247	.9991	.9979	<b>QFI-1618-24</b>
1 1/8	1 9/32	3/4	1.5620	.0780	1.1288	1.1254	1.2818	1.2808	1.1238	1.1226	<b>QFI-1820-12</b>
1 1/8	1 9/32	1 1/2	1.5620	.0780	1.1288	1.1254	1.2818	1.2808	1.1238	1.1226	<b>QFI-1820-24</b>
1 1/4	1 13/32	1 1/4	1.6870	.0780	1.2548	1.2508	1.4068	1.4058	1.2488	1.2472	<b>QFI-2022-20</b>
1 1/4	1 13/32	1 1/2	1.6870	.0780	1.2548	1.2508	1.4068	1.4058	1.2488	1.2472	<b>QFI-2022-24</b>
1 1/2	1 21/32	1 1/2	2.0000	.0780	1.5048	1.5008	1.6568	1.6558	1.4988	1.4972	<b>QFI-2426-24</b>
1 3/4	1 15/16	2	2.3750	.0930	1.7547	1.7507	1.9381	1.9371	1.7487	1.7471	<b>QFI-2831-32</b>
2	2 3/16	2	2.6250	.0930	2.0057	2.0011	2.1883	2.1871	1.9981	1.9969	<b>QFI-3235-32</b>
2 1/4	2 7/16	2	2.7500	.0930	2.2577	2.2531	2.4377	2.4365	2.2507	2.2489	<b>QFI-3639-32</b>

**iglidur® Q2** Kapitel ▶ Seite 415

d1	d2	b1	d3	b2	d1 <sup>3)</sup>		Einpressbohrung		Wellenmaße		Art.-Nr.
					max.	min.	max.	min.	max.	min.	
1/8	3/16	3/16	.3120	.0320	.1269	.1251	.1878	.1873	.1243	.1236	<b>Q2FI-0203-03</b>
3/16	1/4	1/4	.3750	.0320	.1892	.1873	.2503	.2497	.1865	.1858	<b>Q2FI-0304-04</b>
1/4	5/16	3/8	.5000	.0320	.2521	.2498	.3128	.3122	.2490	.2481	<b>Q2FI-0405-06</b>
1/4	5/16	1/2	.5000	.0320	.2521	.2498	.3128	.3122	.2490	.2481	<b>Q2FI-0405-08</b>
5/16	3/8	1/4	.5620	.0320	.3148	.3125	.3753	.3747	.3115	.3106	<b>Q2FI-0506-04</b>
5/16	3/8	3/8	.5620	.0320	.3148	.3125	.3753	.3747	.3115	.3106	<b>Q2FI-0506-06</b>
5/16	3/8	1/2	.5620	.0320	.3148	.3125	.3753	.3747	.3115	.3106	<b>Q2FI-0506-08</b>
3/8	15/32	1/4	.6870	.0460	.3773	.3750	.4691	.4684	.3740	.3731	<b>Q2FI-0607-04</b>
3/8	15/32	3/8	.6870	.0460	.3773	.3750	.4691	.4684	.3740	.3731	<b>Q2FI-0607-06</b>
3/8	15/32	1/2	.6870	.0460	.3773	.3750	.4691	.4684	.3740	.3731	<b>Q2FI-0607-08</b>
3/8	15/32	3/4	.6870	.0460	.3773	.3750	.4691	.4684	.3740	.3731	<b>Q2FI-0607-12</b>
7/16	17/32	1/2	.7500	.0460	.4406	.4379	.5316	.5309	.4365	.4355	<b>Q2FI-0708-08</b>
1/2	19/32	1/4	.8750	.0460	.5030	.5003	.5941	.5934	.4990	.4980	<b>Q2FI-0809-04</b>
1/2	19/32	3/8	.8750	.0460	.5030	.5003	.5941	.5934	.4990	.4980	<b>Q2FI-0809-06</b>
1/2	19/32	1/2	.8750	.0460	.5030	.5003	.5941	.5934	.4990	.4980	<b>Q2FI-0809-08</b>
1/2	19/32	3/4	.8750	.0460	.5030	.5003	.5941	.5934	.4990	.4980	<b>Q2FI-0809-12</b>
1/2	19/32	1	.8750	.0460	.5030	.5003	.5941	.5934	.4990	.4980	<b>Q2FI-0809-16</b>
5/8	23/32	1/2	.9370	.0460	.6280	.6253	.7192	.7184	.6240	.6230	<b>Q2FI-1011-08</b>
5/8	23/32	3/4	.9370	.0460	.6280	.6253	.7192	.7184	.6240	.6230	<b>Q2FI-1011-12</b>
5/8	23/32	1	.9370	.0460	.6280	.6253	.7192	.7184	.6240	.6230	<b>Q2FI-1011-16</b>
3/4	7/8	1/2	1.1250	.0620	.7541	.7505	.8755	.8747	.7491	.7479	<b>Q2FI-1214-08</b>
3/4	7/8	3/4	1.1250	.0620	.7541	.7505	.8755	.8747	.7491	.7479	<b>Q2FI-1214-12</b>
3/4	7/8	1	1.1250	.0620	.7541	.7505	.8755	.8747	.7491	.7479	<b>Q2FI-1214-16</b>
7/8	1	1/2	1.2500	.0620	.8791	.8757	1.0005	.9997	.8741	.8729	<b>Q2FI-1416-08</b>
7/8	1	3/4	1.2500	.0620	.8791	.8757	1.0005	.9997	.8741	.8729	<b>Q2FI-1416-12</b>
7/8	1	1	1.2500	.0620	.8791	.8757	1.0005	.9997	.8741	.8729	<b>Q2FI-1416-16</b>
1	1 1/8	1/2	1.3750	.0620	1.0041	1.0007	1.1255	1.1247	.9991	.9979	<b>Q2FI-1618-08</b>
1	1 1/8	3/4	1.3750	.0620	1.0041	1.0007	1.1255	1.1247	.9991	.9979	<b>Q2FI-1618-12</b>

<sup>3)</sup> nach dem Einpressen. Messverfahren ▶ Seite 57

d1	d2	b1	d3	b2	d1 <sup>3)</sup>		Einpressbohrung		Wellenmaße		Art.-Nr.
					max.	min.	max.	min.	max.	min.	
1	1 1/8	1	1.3750	.0620	1.0041	1.0007	1.1255	1.1247	.9991	.9979	<b>Q2FI-1618-16</b>
1 1/4	1 13/32	1	1.6870	.0780	1.2548	1.2508	1.4068	1.4058	1.2488	1.2472	<b>Q2FI-2022-16</b>
1 1/4	1 13/32	1 1/4	1.6870	.0780	1.2548	1.2508	1.4068	1.4058	1.2488	1.2472	<b>Q2FI-2022-20</b>
1 1/2	1 21/32	1	2.0000	.0780	1.5048	1.5008	1.6568	1.6558	1.4988	1.4972	<b>Q2FI-2426-16</b>
1 1/2	1 21/32	1 1/2	2.0000	.0780	1.5048	1.5008	1.6568	1.6558	1.4988	1.4972	<b>Q2FI-2426-24</b>
1 3/4	1 15/16	2	2.3750	.0930	1.7547	1.7507	1.9381	1.9371	1.7487	1.7471	<b>Q2FI-2831-32</b>
2	2 3/16	2	2.6250	.0930	2.0057	2.0011	2.1883	2.1871	1.9981	1.9969	<b>Q2FI-3235-32</b>

**iglidur® W300** Kapitel ▶ Seite 153

d1	d2	b1	d3	b2	d1 <sup>3)</sup>		Einpressbohrung		Wellenmaße		Art.-Nr.
					max.	min.	max.	min.	max.	min.	
1/8	3/16	3/16	.3120	.0320	.1269	.1251	.1878	.1873	.1243	.1236	<b>WFI-0203-03</b>
1/8	3/16	1/4	.3120	.0320	.1269	.1251	.1878	.1873	.1243	.1236	<b>WFI-0203-04</b>
1/8	3/16	3/8	.3120	.0320	.1269	.1251	.1878	.1873	.1243	.1236	<b>WFI-0203-06</b>
3/16	1/4	1/8	.3750	.0320	.1892	.1873	.2503	.2497	.1865	.1858	<b>WFI-0304-02</b>
3/16	1/4	1/4	.3750	.0320	.1892	.1873	.2503	.2497	.1865	.1858	<b>WFI-0304-04</b>
3/16	1/4	3/8	.3750	.0320	.1892	.1873	.2503	.2497	.1865	.1858	<b>WFI-0304-06</b>
3/16	1/4	1/2	.3750	.0320	.1892	.1873	.2503	.2497	.1865	.1858	<b>WFI-0304-08</b>
1/4	5/16	1/4	.5000	.0320	.2521	.2498	.3128	.3122	.2490	.2481	<b>WFI-0405-04</b>
1/4	5/16	5/16	.5000	.0320	.2521	.2498	.3128	.3122	.2490	.2481	<b>WFI-0405-05</b>
1/4	5/16	3/8	.5000	.0320	.2521	.2498	.3128	.3122	.2490	.2481	<b>WFI-0405-06</b>
1/4	5/16	1/2	.5000	.0320	.2521	.2498	.3128	.3122	.2490	.2481	<b>WFI-0405-08</b>
1/4	5/16	3/4	.5000	.0320	.2521	.2498	.3128	.3122	.2490	.2481	<b>WFI-0405-12</b>
5/16	3/8	1/4	.5620	.0320	.3148	.3125	.3753	.3747	.3115	.3106	<b>WFI-0506-04</b>
5/16	3/8	3/8	.5620	.0320	.3148	.3125	.3753	.3747	.3115	.3106	<b>WFI-0506-06</b>
5/16	3/8	1/2	.5620	.0320	.3148	.3125	.3753	.3747	.3115	.3106	<b>WFI-0506-08</b>
5/16	3/8	3/4	.5620	.0320	.3148	.3125	.3753	.3747	.3115	.3106	<b>WFI-0506-12</b>
3/8	15/32	1/4	.6870	.0460	.3773	.3750	.4691	.4684	.3740	.3731	<b>WFI-0607-04</b>
3/8	15/32	3/8	.6870	.0460	.3773	.3750	.4691	.4684	.3740	.3731	<b>WFI-0607-06</b>
3/8	15/32	1/2	.6870	.0460	.3773	.3750	.4691	.4684	.3740	.3731	<b>WFI-0607-08</b>
3/8	15/32	3/4	.6870	.0460	.3773	.3750	.4691	.4684	.3740	.3731	<b>WFI-0607-12</b>
7/16	17/32	1/2	.7500	.0460	.4406	.4379	.5316	.5309	.4365	.4355	<b>WFI-0708-08</b>
1/2	19/32	1/4	.8750	.0460	.5030	.5003	.5941	.5934	.4990	.4980	<b>WFI-0809-04</b>
1/2	19/32	3/8	.8750	.0460	.5030	.5003	.5941	.5934	.4990	.4980	<b>WFI-0809-06</b>
1/2	19/32	1/2	.8750	.0460	.5030	.5003	.5941	.5934	.4990	.4980	<b>WFI-0809-08</b>
1/2	19/32	3/4	.8750	.0460	.5030	.5003	.5941	.5934	.4990	.4980	<b>WFI-0809-12</b>
1/2	19/32	1	.8750	.0460	.5030	.5003	.5941	.5934	.4990	.4980	<b>WFI-0809-16</b>
5/8	23/32	1/2	.9370	.0460	.6280	.6253	.7192	.7184	.6240	.6230	<b>WFI-1011-045</b>
5/8	23/32	3/4	.9370	.0460	.6280	.6253	.7192	.7184	.6240	.6230	<b>WFI-1011-08</b>
5/8	23/32	1	.9370	.0460	.6280	.6253	.7192	.7184	.6240	.6230	<b>WFI-1011-12</b>
5/8	23/32	1 1/2	.9370	.0460	.6280	.6253	.7192	.7184	.6240	.6230	<b>WFI-1011-24</b>
3/4	7/8	1/2	1.1250	.0620	.7541	.7507	.8755	.8747	.7491	.7479	<b>WFI-1214-08</b>
3/4	7/8	5/8	1.1250	.0620	.7541	.7507	.8755	.8747	.7491	.7479	<b>WFI-1214-10</b>
3/4	7/8	3/4	1.1250	.0620	.7541	.7507	.8755	.8747	.7491	.7479	<b>WFI-1214-12</b>

<sup>3)</sup> nach dem Einpressen. Messverfahren ▶ Seite 57

d1	d2	b1	d3	b2	d1 <sup>3)</sup>		Einpressbohrung		Wellenmaße		Art.-Nr.
					max.	min.	max.	min.	max.	min.	
3/4	7/8	1	1.1250	.0620	.7541	.7507	.8755	.8747	.7491	.7479	<b>WFI-1214-16</b>
3/4	7/8	1 1/2	1.1250	.0620	.7541	.7507	.8755	.8747	.7491	.7479	<b>WFI-1214-24</b>
7/8	1	1/4	1.2500	.0620	.8791	.8757	1.0005	.9997	.8741	.8729	<b>WFI-1416-04</b>
7/8	1	15/32	1.2500	.0620	.8791	.8757	1.0005	.9997	.8741	.8729	<b>WFI-1416-075</b>
7/8	1	1/2	1.2500	.0620	.8791	.8757	1.0005	.9997	.8741	.8729	<b>WFI-1416-08</b>
7/8	1	23/32	1.2500	.0620	.8791	.8757	1.0005	.9997	.8741	.8729	<b>WFI-1416-115</b>
7/8	1	3/4	1.2500	.0620	.8791	.8757	1.0005	.9997	.8741	.8729	<b>WFI-1416-12</b>
7/8	1	1	1.2500	.0620	.8791	.8757	1.0005	.9997	.8741	.8729	<b>WFI-1416-16</b>
7/8	1	1 1/4	1.2500	.0620	.8791	.8757	1.0005	.9997	.8741	.8729	<b>WFI-1416-20</b>
7/8	1	1 1/2	1.2500	.0620	.8791	.8757	1.0005	.9997	.8741	.8729	<b>WFI-1416-24</b>
7/8	1	5/8	1.2500	.0620	.8791	.8757	1.0005	.9997	.8741	.8729	<b>WFI-141618-10</b>
7/8	1	11/16	1.2500	.0620	.8791	.8757	1.0005	.9997	.8741	.8729	<b>WFI-141620-11</b>
1	1 1/8	1/2	1.3750	.0620	1.0041	1.0007	1.1255	1.1247	.9991	.9979	<b>WFI-1618-08</b>
1	1 1/8	3/4	1.3750	.0620	1.0041	1.0007	1.1255	1.1247	.9991	.9979	<b>WFI-1618-12</b>
1	1 1/8	1	1.3750	.0620	1.0041	1.0007	1.1255	1.1247	.9991	.9979	<b>WFI-1618-16</b>
1	1 1/8	1 1/4	1.3750	.0620	1.0041	1.0007	1.1255	1.1247	.9991	.9979	<b>WFI-1618-20</b>
1	1 1/8	1 1/2	1.3750	.0620	1.0041	1.0007	1.1255	1.1247	.9991	.9979	<b>WFI-1618-24</b>
1 1/8	1 9/32	1/2	1.5620	.0780	1.1288	1.1254	1.2818	1.2808	1.1238	1.1226	<b>WFI-1820-08</b>
1 1/8	1 9/32	3/4	1.5620	.0780	1.1288	1.1254	1.2818	1.2808	1.1238	1.1226	<b>WFI-1820-12</b>
1 1/8	1 9/32	1 1/2	1.5620	.0780	1.1288	1.1254	1.2818	1.2808	1.1238	1.1226	<b>WFI-1820-24</b>
1 1/4	1 13/32	3/4	1.6870	.0780	1.2548	1.2508	1.4068	1.4058	1.2488	1.2472	<b>WFI-2022-12</b>
1 1/4	1 13/32	7/8	1.6870	.0780	1.2548	1.2508	1.4068	1.4058	1.2488	1.2472	<b>WFI-2022-14</b>
1 1/4	1 13/32	1	1.6870	.0780	1.2548	1.2508	1.4068	1.4058	1.2488	1.2472	<b>WFI-2022-16</b>
1 1/4	1 13/32	1 1/4	1.6870	.0780	1.2548	1.2508	1.4068	1.4058	1.2488	1.2472	<b>WFI-2022-20</b>
1 1/4	1 13/32	1 1/2	1.6870	.0780	1.2548	1.2508	1.4068	1.4058	1.2488	1.2472	<b>WFI-2022-24</b>
1 3/8	1 17/32	1	1.8750	.0780	1.3798	1.3758	1.5318	1.5308	1.3738	1.3722	<b>WFI-2224-16</b>
1 1/2	1 21/32	3/4	2.0000	.0780	1.5048	1.5008	1.6568	1.6558	1.4988	1.4972	<b>WFI-2426-12</b>
1 1/2	1 21/32	1	2.0000	.0780	1.5048	1.5008	1.6568	1.6558	1.4988	1.4972	<b>WFI-2426-16</b>
1 1/2	1 21/32	1 1/2	2.0000	.0780	1.5048	1.5008	1.6568	1.6558	1.4988	1.4972	<b>WFI-2426-24</b>
1 3/4	1 15/16	1	2.3750	.0930	1.7547	1.7507	1.9381	1.9371	1.7487	1.7471	<b>WFI-2831-16</b>
1 3/4	1 15/16	1 1/2	2.3750	.0930	1.7547	1.7507	1.9381	1.9371	1.7487	1.7471	<b>WFI-2831-24</b>
1 3/4	1 15/16	2	2.3750	.0930	1.7547	1.7507	1.9381	1.9371	1.7487	1.7471	<b>WFI-2831-32</b>
2	2 3/16	1	2.6250	.0930	2.0057	2.0011	2.1883	2.1871	1.9981	1.9969	<b>WFI-3235-16</b>
2	2 3/16	1 1/2	2.6250	.0930	2.0057	2.0011	2.1883	2.1871	1.9981	1.9969	<b>WFI-3235-24</b>
2	2 3/16	2	2.6250	.0930	2.0057	2.0011	2.1883	2.1871	1.9981	1.9969	<b>WFI-3235-32</b>

**iglidur® X** Kapitel ▶ Seite 245

d1	d2	b1	d3	b2	d1 <sup>3)</sup>		Einpressbohrung		Wellenmaße		Art.-Nr.
					max.	min.	max.	min.	max.	min.	
1/8	3/16	3/16	.3120	.0320	.1266	.1247	.1878	.1873	.1243	.1236	<b>XFI-0203-03</b>
1/8	3/16	3/8	.3120	.0320	.1266	.1247	.1878	.1873	.1243	.1236	<b>XFI-0203-06</b>
3/16	1/4	1/4	.3750	.0320	.1888	.1869	.2503	.2497	.1865	.1858	<b>XFI-0304-04</b>
3/16	1/4	3/8	.3750	.0320	.1888	.1869	.2503	.2497	.1865	.1858	<b>XFI-0304-06</b>
3/16	1/4	1/2	.3750	.0320	.1888	.1869	.2503	.2497	.1865	.1858	<b>XFI-0304-08</b>
1/4	5/16	3/16	.5000	.0320	.2518	.2495	.3128	.3122	.2490	.2481	<b>XFI-0405-03</b>

<sup>3)</sup> nach dem Einpressen. Messverfahren ▶ Seite 57

d1	d2	b1	d3	b2	d1 <sup>3)</sup>		Einpressbohrung		Wellenmaße		Art.-Nr.
					max.	min.	max.	min.	max.	min.	
1/4	5/16	1/4	.5000	.0320	.2518	.2495	.3128	.3122	.2490	.2481	<b>XFI-0405-04</b>
1/4	5/16	3/8	.5000	.0320	.2518	.2495	.3128	.3122	.2490	.2481	<b>XFI-0405-06</b>
1/4	5/16	1/2	.5000	.0320	.2518	.2495	.3128	.3122	.2490	.2481	<b>XFI-0405-08</b>
1/4	5/16	3/4	.5000	.0320	.2518	.2495	.3128	.3122	.2490	.2481	<b>XFI-0405-12</b>
5/16	3/8	1/4	.5620	.0320	.3143	.3120	.3753	.3747	.3115	.3106	<b>XFI-0506-04</b>
5/16	3/8	3/8	.5620	.0320	.3143	.3120	.3753	.3747	.3115	.3106	<b>XFI-0506-06</b>
5/16	3/8	1/2	.5620	.0320	.3143	.3120	.3753	.3747	.3115	.3106	<b>XFI-0506-08</b>
3/8	15/32	1/4	.6870	.0460	.3768	.3745	.4691	.4684	.3740	.3731	<b>XFI-0607-04</b>
3/8	15/32	3/8	.6870	.0460	.3768	.3745	.4691	.4684	.3740	.3731	<b>XFI-0607-06</b>
3/8	15/32	1/2	.6870	.0460	.3768	.3745	.4691	.4684	.3740	.3731	<b>XFI-0607-08</b>
3/8	15/32	3/4	.6870	.0460	.3768	.3745	.4691	.4684	.3740	.3731	<b>XFI-0607-12</b>
7/16	17/32	1/2	.7500	.0460	.4399	.4371	.5316	.5309	.4365	.4355	<b>XFI-0708-08</b>
1/2	19/32	1/4	.8750	.0460	.5024	.4996	.5941	.5934	.4990	.4980	<b>XFI-0809-04</b>
1/2	19/32	3/8	.8750	.0460	.5024	.4996	.5941	.5934	.4990	.4980	<b>XFI-0809-06</b>
1/2	19/32	1/2	.8750	.0460	.5024	.4996	.5941	.5934	.4990	.4980	<b>XFI-0809-08</b>
1/2	19/32	3/4	.8750	.0460	.5024	.4996	.5941	.5934	.4990	.4980	<b>XFI-0809-12</b>
1/2	19/32	1	.8750	.0460	.5024	.4996	.5941	.5934	.4990	.4980	<b>XFI-0809-16</b>
5/8	23/32	1/2	.9370	.0460	.6274	.6246	.7192	.7184	.6240	.6230	<b>XFI-1011-08</b>
5/8	23/32	3/4	.9370	.0460	.6274	.6246	.7192	.7184	.6240	.6230	<b>XFI-1011-12</b>
5/8	23/32	1	.9370	.0460	.6274	.6246	.7192	.7184	.6240	.6230	<b>XFI-1011-16</b>
5/8	23/32	1 1/2	.9370	.0460	.6274	.6246	.7192	.7184	.6240	.6230	<b>XFI-1011-24</b>
3/4	7/8	1/2	1.1250	.0620	.7532	.7499	.8755	.8747	.7491	.7479	<b>XFI-1214-08</b>
3/4	7/8	3/4	1.1250	.0620	.7532	.7499	.8755	.8747	.7491	.7479	<b>XFI-1214-12</b>
3/4	7/8	1	1.1250	.0620	.7532	.7499	.8755	.8747	.7491	.7479	<b>XFI-1214-16</b>
3/4	7/8	1 3/4	1.1250	.0620	.7532	.7499	.8755	.8747	.7491	.7479	<b>XFI-1214-28</b>
7/8	1	1/2	1.2500	.0620	.8782	.8749	1.0005	.9997	.8741	.8729	<b>XFI-1416-08</b>
7/8	1	3/4	1.2500	.0620	.8782	.8749	1.0005	.9997	.8741	.8729	<b>XFI-1416-12</b>
7/8	1	1	1.2500	.0620	.8782	.8749	1.0005	.9997	.8741	.8729	<b>XFI-1416-16</b>
1	1 1/8	1/2	1.3750	.0620	1.0032	.9999	1.1255	1.1247	.9991	.9979	<b>XFI-1618-08</b>
1	1 1/8	3/4	1.3750	.0620	1.0032	.9999	1.1255	1.1247	.9991	.9979	<b>XFI-1618-12</b>
1	1 1/8	1	1.3750	.0620	1.0032	.9999	1.1255	1.1247	.9991	.9979	<b>XFI-1618-16</b>
1	1 1/8	1 1/2	1.3750	.0620	1.0032	.9999	1.1255	1.1247	.9991	.9979	<b>XFI-1618-24</b>
1 1/8	1 9/32	3/4	1.5620	.0780	1.1288	1.1254	1.2818	1.2808	1.1238	1.1226	<b>XFI-1820-12</b>
1 1/4	1 13/32	1	1.6870	.0780	1.2537	1.2498	1.4068	1.4058	1.2488	1.2472	<b>XFI-2022-16</b>
1 1/4	1 13/32	1 1/4	1.6870	.0780	1.2537	1.2498	1.4068	1.4058	1.2488	1.2472	<b>XFI-2022-20</b>
1 1/4	1 13/32	2	1.6870	.0780	1.2537	1.2498	1.4068	1.4058	1.2488	1.2472	<b>XFI-2022-32</b>
1 1/2	1 21/32	3/4	2.0000	.0780	1.5048	1.5008	1.6568	1.6558	1.4988	1.4972	<b>XFI-2426-12</b>
1 1/2	1 21/32	1	2.0000	.0780	1.5048	1.5008	1.6568	1.6558	1.4988	1.4972	<b>XFI-2426-16</b>
1 1/2	1 21/32	1 1/2	2.0000	.0780	1.5048	1.5008	1.6568	1.6558	1.4988	1.4972	<b>XFI-2426-24</b>
1 1/2	1 21/32	1 5/8	2.0000	.0780	1.5048	1.5008	1.6568	1.6558	1.4988	1.4972	<b>XFI-2426-26</b>
1 3/4	1 15/16	1	2.3750	.0930	1.7536	1.7497	1.9381	1.9371	1.7487	1.7471	<b>XFI-2831-16</b>
1 3/4	1 15/16	2	2.3750	.0930	1.7536	1.7497	1.9381	1.9371	1.7487	1.7471	<b>XFI-2831-32</b>
2	2 3/16	2	2.6250	.0930	2.0057	2.0011	2.1883	2.1871	1.9981	1.9969	<b>XFI-3235-32</b>
2 3/4	2 15/16	2	3.3750	.0930	2.7570	2.7523	2.9370	2.9358	2.7500	2.7490	<b>XFI-4447-32</b>

<sup>3)</sup> nach dem Einpressen. Messverfahren ▶ Seite 57