




# Blind Rivet Nut ESM-R

## Series 10.865

### Stainless Steel A2

- > Countersunk Head
- > Round Shank
- > Open
- > Knurled



[1.4567]

M		l	No.	
<b>M3</b>	2,0 - 3,5	10,5	10.865.030.350	500
<b>D</b> 5,0	<b>k</b> 1,0	<b>d<sub>k</sub></b> 8,0	<b>l<sub>1</sub> max.</b> 6,5	<b>↓</b> 3700 N
<b>M4</b>	1,5 - 4,0	12,0	10.865.040.400	500
<b>D</b> 6,0	<b>k</b> 1,0	<b>d<sub>k</sub></b> 9,0	<b>l<sub>1</sub> max.</b> 8,0	<b>↓</b> 6500 N
<b>M5</b>	1,5 - 4,5	13,5	10.865.050.450	500
<b>D</b> 7,0	<b>k</b> 1,0	<b>d<sub>k</sub></b> 10,0	<b>l<sub>1</sub> max.</b> 8,5	<b>↓</b> 10000 N

M		l	No.	
<b>M6</b>	1,5 - 4,5 4,5 - 6,5	16,0 18,0	10.865.060.450 10.865.060.650	500 500
<b>D</b> 9,0	<b>k</b> 1,0	<b>d<sub>k</sub></b> 12,0	<b>l<sub>1</sub> max.</b> 10,0	<b>↓</b> 15000 N
<b>M8</b>	1,5 - 4,5 4,5 - 6,5	18,0 20,0	10.865.080.450 10.865.080.650	500 250
<b>D</b> 11,0	<b>k</b> 1,5	<b>d<sub>k</sub></b> 14,0	<b>l<sub>1</sub> max.</b> 12,0	<b>↓</b> 25000 N
<b>M10</b>	2,0 - 4,5	21,0	10.865.100.450	250
<b>D</b> 13,0	<b>k</b> 1,6	<b>d<sub>k</sub></b> 16,0	<b>l<sub>1</sub> max.</b> 14,5	<b>↓</b> 38000 N