



# TYPE APPROVAL CERTIFICATE

Certificate No:  
**TAE000037X**  
Revision No:  
**1**

## This is to certify:

**That the Cable Gland**

with type designation(s)

**PERFECT 50.6xx PAzzzz, PERFECT 50.6xx PA/FLzzzz, Locknut 50.2xx PAzzzz, Locknut 50.2xx PA/FLzzzz**

Issued to

**Jacob GmbH Elektrotechnische Fabrik  
Kernen im Remstal, Baden-Württemberg, Germany**

is found to comply with

**DNV rules for classification – Ships, offshore units, and high speed and light craft**

## Application :

**Product(s) approved by this certificate is/are accepted for installation on all vessels classed by DNV.**

Type	Material	Suitable for open deck	Suitable for Hazardous areas
<b>PERFECT 50.6xx PAzzzz</b>	<b>Plastic</b>	<b>Yes</b>	<b>n/a</b>
<b>PERFECT 50.6xx PA/FLzzzz</b>	<b>Plastic</b>	<b>Yes</b>	<b>n/a</b>
<b>Locknut 50.2xx PAzzzz</b>	<b>Plastic</b>	<b>Yes</b>	<b>n/a</b>
<b>Locknut 50.2xx PA/FLzzzz</b>	<b>Plastic</b>	<b>Yes</b>	<b>n/a</b>

Issued at **Høvik** on **2023-10-18**

for **DNV**

This Certificate is valid until **2028-10-17**.

DNV local unit: **Augsburg**

Approval Engineer: **Maik Gagern**

.....  
**Oddvar Deinboll**  
**Head of Section**

This Certificate is subject to terms and conditions overleaf. Any significant change in design or construction may render this Certificate invalid. The validity date relates to the Type Approval Certificate and not to the approval of equipment/systems installed.

LEGAL DISCLAIMER: Unless otherwise stated in the applicable contract with the holder of this document, or following from mandatory law, the liability of DNV AS, its parent companies and their subsidiaries as well as their officers, directors and employees ("DNV") arising from or in connection with the services rendered for the purpose of the issuance of this document or reliance thereon, whether in contract or in tort (including negligence), shall be limited to direct losses and under any circumstance be limited to 300,000 USD.



## Product description

### Cable Glands:

PERFECT 50.6xx PAzzzz, PERFECT 50.6xx PA/FLzzzz

#### Nomenclature:

xx = place holder for connecting thread size „12“, „16“, „20“, „25“, „32“, „40“, „50“, „63“ (M12x1,5 to M63x1,5 /metric, as per EN 60423)

zzzz = place holder for color with RAL no. „7001“, „7035“, „9005“ or in other way, e.g. for black „SW“

optional suffix: other thread length, e.g. „L“, „08“; other details, e.g. bending protection „BS“

### Locknuts:

50.2xx PAzzzz, 50.2xx PA/FLzzzz

#### Nomenclature:

xx = place holder for connecting thread size „12“, „16“, „20“, „25“, „32“, „40“, „50“, „63“ (M12x1,5 to M63x1,5 /metric, as per EN 60423)

zzzz = place holder for color with RAL no. „7001“, „7035“, „9005“ or in other way, e.g. for black „SW“;

## Application/Limitation

Installation and operating instructions of the manufacturer to be observed.

## Type Approval documentation

[Jacob\\_PERFECT cable gland\\_Plastic\\_DNV-GL\\_Product description\\_2018-08-06.pdf \(45 Pages\)](#)

## Tests carried out

Acc. to DNV Class Programme DNV-CP-0408 (2021-09) / EN 62444 (2013)

## Marking of product



Jacob GmbH registered trademark (Letters WJ) on smallest packaging unit and / or on the product.  
Type designation / size on smallest packaging unit

## Periodical assessment

The scope of the periodical assessment is to verify that the conditions stipulated for the Type approval are complied with and that no alterations are made to the product design or choice of materials.

The main elements of the assessment are:

- Inspection on factory samples, selected at random from the production line (where practicable)
- Results from Routine Tests (RT) checked (if not available tests according to RT to be carried out)
- Review of type approval documentation
- Review of possible change in design, materials and performance
- Ensuring traceability between manufacturer's product type marking and Type Approval Certificate.

Periodical assessment is to be performed after 2 years and after 3.5 years. A renewal assessment will be performed at renewal of the certificate.

## END OF CERTIFICATE