



悬臂销 法兰型 扣环型 · 螺帽固定型

code 追加加工
天发货 天发货

选型指南



举例	型号	Y	F	M
标准	Code	D		
扣环型	XBX35CB 12 - 23 - F15			
螺帽固定型	XBX39CB 12 - 24 - F15 - M8			

扣环型



●圆型


●侧切型





注: XBX35CB、XBX36CB 以外型号的R0.2部分为退刀槽

型号		指定单位1mm		V	Ha	T	m1	d1	h	P. C. D.	d容差		m	n	W	A							
Code	Dg6	Y	F																				
圆法兰型 XBX35CB XBX35CN XBX35S	6	-0.004 -0.012	12~60	5~100	8	26	10	M4	6.5	3.6	17	5	+0.075 0	0.7	2	14	17						
	8	-0.005 -0.014			10	28					19	7	+0.090 0					1.15	3	15	19		
	10	-0.005 -0.014			13	32					23	9.6	0 -0.090									4	16
侧切法兰型 XBX36CB XBX36CN XBX36S	12	-0.006 -0.017	10~150	10~150	15	36	15	M5	8	4.5	26	11.5	0	1.35	4	20	26						
	15	-0.006 -0.017			18	40					30	14.3	-0.110					5	24	30			
	20	-0.007 -0.020			24	48					36	19	0								1.65	38	42
	25	-0.007 -0.020			29	54					42	23.9	-0.210					5	42	49			
	30	-0.007 -0.020			34	62					49	28.6											

螺帽固定型



●圆型



注: XBX39CB以外型号的R0.2部分为退刀槽

型号		指定单位1mm		M(粗牙螺纹)选择		V	Ha	T	m1	d1	h	P. C. D.	
Code	Dg6	Y	F										
XBX39CB XBX39CN XBX39S	6	-0.004 -0.012	12~60	5~100	4 5 6	8	26	10	M4	6.5	3.6	17	
	8	-0.005 -0.014			5 6 8	10	28						19
	10	-0.005 -0.014			6 8 10	13	32						
	12	-0.006 -0.017	10~150	10~150	6 8 10 12	15	36	M5	8	4.5	26		
	15	-0.006 -0.017			8 10 12 15	18	40					30	
	20	-0.007 -0.020			10 12 15 16	24	48						M 6
25	-0.007 -0.020	10 12 16 20 24	29	54	42								
30	-0.007 -0.020	12 16 20 24 30	34	62		M 8	11	6.6	49				