


Part No. structure



Series E16 - split crossbar along the outer radius

Part No.	Bending radii			Weight [kg/m]
	B_i [mm]	B_a [mm]	R [mm]	
E16.2. <input type="text"/> .0	23	37,5	<input type="text"/> 060 <input type="text"/> 075 <input type="text"/> 100	≈ 0,51
E16.3. <input type="text"/> .0	36	50,5	<input type="text"/> 060 <input type="text"/> 075 <input type="text"/> 100	≈ 0,57
E16.4. <input type="text"/> .0	48	62,5	<input type="text"/> 060 <input type="text"/> 075 <input type="text"/> 100	≈ 0,62
E16.5. <input type="text"/> .0	63	78,5	<input type="text"/> 060 <input type="text"/> 075 <input type="text"/> 100	≈ 0,75
E16.6. <input type="text"/> .0	80	95,5	<input type="text"/> 060 <input type="text"/> 075 <input type="text"/> 100	≈ 0,83
E16.7. <input type="text"/> .0	100	115,3	<input type="text"/> 060 <input type="text"/> 075 <input type="text"/> 100	≈ 0,91



B_a : pin dimension approx. 0,3 - 0,7 mm wider

The bending radius 125 is available upon request.


Delivery time: approx. 3-4 weeks after receipt of order!

Supplement Part No. with required radius. Example: E16.3. 060 .0

0 = standard color, other colors ► page 1.39 · Pitch = 30,5 mm/link - Links/m = 33



Part No. structure



Series Z16 - split crossbar along the inner radius

Part No.	Bending radii			Weight [kg/m]
	B_i [mm]	B_a [mm]	R [mm]	
Z16.2. <input type="text"/> .0	23	37,5	<input type="text"/> 060 <input type="text"/> 075 <input type="text"/> 100	≈ 0,51
Z16.3. <input type="text"/> .0	36	50,5	<input type="text"/> 040 <input type="text"/> 060 <input type="text"/> 075 <input type="text"/> 100	≈ 0,57
Z16.4. <input type="text"/> .0	48	62,5	<input type="text"/> 040 <input type="text"/> 060 <input type="text"/> 075 <input type="text"/> 100	≈ 0,62
Z16.5. <input type="text"/> .0	63	78,5	<input type="text"/> 060 <input type="text"/> 075 <input type="text"/> 100	≈ 0,75
Z16.6. <input type="text"/> .0	80	95,5	<input type="text"/> 060 <input type="text"/> 075 <input type="text"/> 100	≈ 0,83
Z16.7. <input type="text"/> .0	100	115,3	<input type="text"/> 060 <input type="text"/> 075 <input type="text"/> 100	≈ 0,91

B_a : pin dimension approx. 0,3 - 0,7 mm wider

The bending radius 125 is available upon request.

Delivery time: approx. 3-4 weeks after receipt of order!

Supplement Part No. with required radius. Example: Z16.3. 060 .0

0 = standard color, other colors ► page 1.39 · Pitch = 30,5 mm/link - Links/m = 33

