



齿轮减速电机 标准型 立式 750W

code 5天发货 code 7天发货

选型指南

举例	型号	功率	减速比	类型	刹车	轴径
标准	GL	750	5	S		28



备注: A1 三相马达尺寸; A2 三相刹车马达尺寸

相数	功率	频率 HZ	电压 V	电流 A	回转数 rpm
三相	100W	50/60	220/380	1/0.6	1350/1650
	200W	50/60	220/380	1.2/0.8	1350/1650
	400W	50/60	220/380	2.1/1.3	1380/1680
	750W	50/60	220/380	3.5/2.3	1400/1700
	1500W	50/60	220/380	6/3.7	1410/1720
	2200W	50/60	220/380	9/6	1410/1720
单相	100W	50/60	110/220	3.4/1.7	1350/1650
	200W	50/60	110/220	3.6/1.8	1350/1650
	400W	50/60	110/220	7.6/3.8	1350/1650
	750W	50/60	110/220	12/6	1380/1680
	1500W	50/60	110/220	28/14	1400/1700

轴径	A1	A2	D	E	F	G	H	J	K	L	M	V	U	Y	Z	出力轴端					重量 (KG)
																P	Q	S	T	W	
28	374	377	170	218	200	180	11	20.5	59	14	160	154	154	4	123	45	40	28	31	7	16.2
32	411	414	185	255	233	210	13	30.3	70	18	160	180.3	180	4	123	55	50	32	35.5	10	32.5
40	462	465	230	310	298	270	15	42	77	20	160	219	219	5	123	65	60	40	43.5	10	55

型号	功率 W	减速比	类型	刹车	轴径	输出转速 rpm		输出扭矩 kg.m		出力轴垂直负荷 KG		实际速比
						50HZ	60HZ	50HZ	60HZ	50HZ	60HZ	
GL	750	5	A: 单相110V C: 单相220V S: 三相 220V/380V	B: 带刹车 空: 无刹车	28	300	360	2.2	1.9	85	75	4.35
		28			150	180	4.5	3.8	180	150	11.25	
		28			100	120	6.8	5.7	165	160	16.15	
		28			75	90	9.0	7.5	175	170	19.93	
		28			60	72	11.2	9.4	185	180	22.40	
		32			50	60	13.5	11.3	415	400	29.33	
		32									31.09	
		28									41.09	
		32			38	45	17.5	14.6	430	420	41.28	
		28									50.33	
		32			30	36	21.9	18.3	450	440	51.60	
		28									63.35	
		32			25	30	26.2	21.9	450	450	60.23	
		28									72.25	
		32			21	25	31.5	26.3	460	460	70.49	
		28									80.75	
		32			18	22	35.5	29.6	460	460	83.31	
		28									90.95	
		32			16	20	39.3	32.8	500	500	92.57	
		32			15	18	43.2	36.0	590	590	101.21	
32	12	15	51.8	43.2	640	640	115.71					
32							145.02					
40	11	13	59.7	49.8	679	679	139.83					
32							161.03					
40	9	11	68.0	56.7	700	700	159.44					
32							181.27					
40	8	10	76.8	64.0	720	720	180.70					
32							201.28					
40	7	9	82.8	69.0	720	720	208.52					

电气部品

加热器

坦克链

电缆
固定头

线缆
保护管

探针

传感器
导轨

传感器
遮光片

步进
驱动器

步进电机

小型
调速电机

齿轮
减速电机

按钮开关

端子台