


## Series Z26 - split crossbar along the inner radius

Part No.	Bi [mm]	Ba [mm]	R [mm]	Bending radii	Weight [kg/m]
Z26.07. <input type="text"/> .0	75	92	063	075 100 125 150 175 200 250	≈ 0,96

Ba: pin dimension approx. 0,3 - 0,5 mm wider!

Supplement Part No. with required radius. Example: Z26.07.  150 .0

0 = standard color, other colors ▶ page 1.39 · Pitch = 56 mm/link - Links/m = 18




## Series Z26 - split crossbar along the inner radius with 2-chamber system

Part No.	Bi [mm]	Ba [mm]	R [mm]	Bending radii	Weight [kg/m]
Z26.2/45. <input type="text"/> .0	48/48	117	063	075 100 125 150 175 200 250	≈ 1,14

Ba: pin dimension approx. 0,3 - 0,5 mm wider!

Supplement Part No. with required radius. Example: Z26.2/45.  150 .0

0 = standard color, other colors ▶ page 1.39 · Pitch = 56 mm/link - Links/m = 18





## Series Z26 - split crossbar along the inner radius with 3-chamber system

Part No.	Bi [mm]	Ba [mm]	R [mm]	Bending radii	Weight [kg/m]
Z26.3/45. <input type="text"/> .0	47/48/47	167	063	075 100 125 150 175 200 250	≈ 1,30

Ba: pin dimension approx. 0,3 - 0,5 mm wider!

Supplement Part No. with required radius. Example: Z26.3/45.  150 .0

0 = standard color, other colors ▶ page 1.39 · Pitch = 56 mm/link - Links/m = 18



Part No. structure

Z26.	07.	150.	0
------	-----	------	---

Color  
black  
Bending  
radius  
Width  
Series

Easy Chain®  
Inner height: 36,5 mm

Phone +49- (0) 22 03-96 49-800  
Fax +49- (0) 22 03-96 49-222



▶ page 3.5