


锁销\绝缘定位销

选型指南

举例	型号		型号		- L
	Code	No.	Code	D	
标准	KJNPN	10	MSSIP	6	- 25

Code	材质	表面处理
KJNPN	SWRH6	铬酸盐光泽处理
KJNPNS	SUS304	-


锁销



型号		d (线径)	d1	La	L1	L2	R	h	S	D1 (适用轴径)	D2 (轴孔径)
Code	No.										
KJNPN KJNPNS	4	1	3	16.3	6	1.5	2	1	0.5	4	1.2
	5			17.9	6.5		2.5	1.5		5	
	6	1.2	3.6	21.2	7.8		3	1.8	0.6	6	1.5
	8	1.6	4.8	27.7	10.4		4	2.4	0.8	8	1.9
	10	1.8	5.4	32.6	12.2		5	3.2	0.9	10	2.2
	12			35.8	13.2		6	4.2		12	

绝缘定位销

Code	材质	
	主体	芯
MSSIP	树脂	SUS304



Code	型号		D公差	d1	L
	D				
MSSIP	6	+0.03 0	3	4	8 10 15 20 25 30 35 40
	8				10 15 20 25 30 35 40
	9				15 20 25 30 35 40 45 50
	10				15 20 25 30 35 40 45 50
	12				20 25 30 35 40 45 50

圆线弹簧

拉簧

扭簧 碟簧
氮气弹簧

矩形弹簧

扣环

平键

销子

磁铁

小零件

密封圈

垫圈

轴环

精密垫片

螺丝

螺母
垫圈