


Part No. structure



Series 045 E-Chain® - non snap-open

Part No.	B_i [mm]	B_a [mm]	R [mm]	Bending radii	Weight [kg/m]
045.06. <input type="text"/> .0	6	12	<input type="text"/> 018 <input type="text"/> 028 <input type="text"/> 038		≈ 0,09
045.10. <input type="text"/> .0	10	16	<input type="text"/> 018 <input type="text"/> 028 <input type="text"/> 038		≈ 0,10
045.16. <input type="text"/> .0	16	22	<input type="text"/> 018 <input type="text"/> 028 <input type="text"/> 038		≈ 0,11
045.20. <input type="text"/> .0	20	26	<input type="text"/> 018 <input type="text"/> 028 <input type="text"/> 038		≈ 0,13
045.30. <input type="text"/> .0	30	36	<input type="text"/> 018 <input type="text"/> 028 <input type="text"/> 038		≈ 0,16
045.64. <input type="text"/> .0	64	70	<input type="text"/> 018 <input type="text"/> 028 <input type="text"/> 038		≈ 0,19

 Supplement Part No. with required radius. Example: 045.20. 038 .0

0 = standard color, other colors ► page 1.39 · Pitch = 13 mm/link - Links/m = 77

