

Interior installation

Component shelves for attachment to the 19" system punchings



Component shelf, static installation

482.6 mm (19"), depth-variable for TS-IT

For static installation between two 482.6 mm (19") mounting levels.

- Depth-variable to adapt to individual distances between levels
- Toolless, time-saving one-man assembly

Material:

- Sheet steel

Surface finish:

- Spray-finished

Colour:

- RAL 9005

Supply includes:

- Assembly parts

Distance between levels mm	Load capacity, static kg	Height U	Packs of	Model No.
400 – 600	50	½	1 set(s)	5501.655
600 – 900	50	½	1 set(s)	5501.665
400 – 600	100	1	1 set(s)	5501.695
600 – 900	100	1	1 set(s)	5501.705



Component shelf, pull-out

482.6 mm (19") for TS-IT

For mounting between two 482.6 mm (19") mounting levels.

- Depth-variable to adapt to individual distances between levels
- Toolless, time-saving one-man assembly from the enclosure front
- Self-locking
- Full withdrawal

Material:

- Sheet steel

Surface finish:

- Spray-finished

Colour:

- RAL 9005

Supply includes:

- Component shelf, slotted
- Telescopic slide with mounting kit
- Assembly parts

Distance between levels mm	Load capacity, static kg	Height U	Depth mm	Packs of	Model No.
400 – 600	50	1	500	1 set(s)	5501.675
600 – 900	50	1	700	1 set(s)	5501.685
400 – 600	100	1½	500	1 set(s)	5501.715
600 – 900	100	1½	700	1 set(s)	5501.725

+ Accessories:

- Handle for component shelf 5501.730, see page 633



Component shelf 1 U, static installation

482.6 mm (19") for 482.6 mm (19") system punchings

The ideal support surface for small active components such as modems or mini-hubs in 482.6 mm (19") or metric levels.

Load capacity:

- 10 kg surface load, static

Material:

- Sheet steel

Colour:

- RAL 7035

Note:

- Cannot be combined with server telescopic slides
- Free installation height inside the U approx. 35 mm

Component shelf depth mm	Model No.
140	7119.140

! Also required:

- Captive nuts, see page 624
- Screws, see page 625

