

Part No. structure

E3.22.060.044.0



Series E3.22 - snap-open along outer radius

Part No.	B_i [mm]	B_a [mm]	R [mm]	Bending radii			Weight [kg/m]
E3.22.020.□.0	20	32	044	050	075	≈ 0,30	
E3.22.040.□.0	40	52	044	050	075	≈ 0,32	
E3.22.060.□.0	60	72	044	050	075	≈ 0,41	

The bending radius **050** is available upon request for Series E3.22.060

Delivery time: approx. 6-8 weeks after receipt of order!

Supplement Part No. with required radius. Example: E3.22.060.044.0

0 = standard color, other colors ► page 1.39 · Pitch = 16,7 mm/link - Links/m = 60




E3 | Series E3.22 | Accessories | Interior Separation

Vertical separator,
slotted (single)

unassembled E3.22.01

assembled E3.22.11



Vertical separators

Vertical separators are used if a vertical subdivision of the E-Chain® interior is required -

- Subdivision with vertical separator E3.22.11 (slotted 3 times)

