

Industrial Workstations



System accessories Page 507 Comfort Panel Page 124 Optipanel Page 126 TFT monitor Page 706

Material:

- Enclosure, roof, drawer tray, designer door, rear wall and rear door: Sheet steel
- Worktop: Chipboard, plastic-laminated on both sides (edging)
- Handle: Aluminium, powder-coated

Surface finish:

- Enclosure: Dipcoat-primed, powder-coated on the outside, textured paint

Colour:

- Enclosure, worktop: RAL 7035
- Worktop edge strip: RAL 7015
- Worktop handle: RAL 9006

Protection category:

- See table

Supply includes:

- Available on the Internet

Technical details:

- Available on the Internet














Photo shows a configuration example with equipment not included in the scope of supply

Combination options



IW enclosures and worktops

Enclosure										Page	
Version					Designer door, rear panel screw-fastened from the inside	Designer door, rear door	Drawer section, designer door, rear door	Drawer section for keyboard and mouse, designer door, rear door	Worktop, keyboard drawer, designer door, rear door		
Width (B) mm					600	600	600	600	600		
Height (H) mm					900	900	900	900	1000		
Depth (T) mm					600	600	600 (890)	600 (890)	645		
Weight (kg)					54.9	59.9	73	73	91		
Model No.					6900.000	6900.100	6900.400	6900.410	6901.100		
Protection category IP to IEC 60 529					IP 55			IP 54			
Protection category NEMA					NEMA 12			NEMA 12			
	Width (B) mm	Height (H) mm	Depth (T) mm	Weight kg	Model No.						
Worktops											
	610	38	645	11.6	6902.300	6902.300	–	–	■		
	1000	38	895	24	6902.100	6902.100	6902.100	6902.100	–		
Monitor housing											
	600	600	600	42.5	6902.500	6902.500	6902.500	6902.500	–		
Accessories					Packs of						
Base/plinth, stationary					1 pc(s).	8800.920	8800.920	8800.920	8800.920	8800.920	517
Cross member, adjustable					2 pc(s).	8601.680	8601.680	8601.680	8601.680	–	520
Twin castors					1 set(s)	7495.000	7495.000	7495.000	7495.000	7495.000	522
Handle adaptor for comfort handle					1 pc(s).	8611.300	8611.300	–	–	–	549
Cable gland					1 pc(s).	6902.770	6902.770	6902.770	6902.770	6902.770	660
Mounting plate for enclosure width 600 mm					1 pc(s).	8614.675	8614.675	8614.675	8614.675	8614.680	596
Component shelf, static installation					1 pc(s).	8800.900	8800.900	8800.900	8800.900	8800.900	628
Component shelf, pull-out					1 pc(s).	6902.960	6902.960	6902.960	6902.960	6902.960	627
Drawer tray					1 pc(s).	6902.700	6902.700	6902.700	6902.700	6902.700	628
Paper removal flap					1 pc(s).	6903.200	6903.200	6903.200	6903.200	6903.200	713
Support arm systems								see page 135			
Command panels								see page 130			